



# The ultimate step in energy saving with TL5 High Output

## MASTER TL5 High Output EcoPlus

TL5 High Output EcoPlus lamp (tube diameter 16 mm) provides extra energy savings by simple lamp-for-lamp replacement of TL5 HO Eco lamps, at the expense of slightly reduced light output. No compromises are made on the excellent TL5 lumen maintenance, lifetime and color rendering. Application areas vary from offices and industry to schools and retail environments.

### 优点

- Up to 20% energy saving simply by changing the lamp
- The same quality of light as from MASTER TL5 HO lamps
- All benefits of regular TL5 lamps

### 特点


- High lamp efficacies up to 107 lm/W
- Up to 20% power reduction compared with standard MASTER TL5 HO lamps and up to 10% compared with TL5 HO Eco lamps

### 应用


- All current non-dimmable TL5 HO indoor applications, e.g. offices, schools, supermarkets, industrial facilities with room temperatures above 20 °C (which means temperatures around the lamp of over 25-30 °C)
- Not recommended for use where there is a strong air flow around the lamps

# MASTER TL5 High Output EcoPlus

## Versions



## 二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm
EcoPlus 44=54W/865					
1SL/40					

