

Product Description

MASTER TL-D Super 80

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Special fluorescent coating gives good colour rendering
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Create atmospheres from warm white to cool daylight

Features

- Highly efficient 3-band fluorescent coating in combination with New Generation pre-coating technology
- High initial light output
- Available in varying colour designations
- Low mercury dose

Application


- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc.

Versions



MASTER TL-D Super 80

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 36W/865 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

