



Seeing colors as they are

MASTER TL-D 90 Graphica

This TL-D lamp has excellent color rendering which makes it very suitable for the graphical and printing industry to check the quality of printed material.

Benefits

- Making representation of colors extremely realistic
- Consistent with the strict standards for the graphical industry defined in standard EN-12464
- Enabling customer to switch to excellent color rendering properties with low decrease of light level

Features

- High-quality fluorescent coating for excellent color rendering and very accurate color point
- Use of mix of three-band phosphors and halophosphates for high efficacy
- Retrofit in current luminaires for standard TL-D lamps

Application

- Used in applications where excellent color rendering is crucial, such as the graphical industry, printing industry, photo shops, hospitals, etc.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.