



Seeing colors as they are

MASTER TL-D 90 Graphica

This TL-D lamp has excellent color rendering which makes it very suitable for the graphical and printing industry to check the quality of printed material.

Benefits

- Making representation of colors extremely realistic
- Consistent with the strict standards for the graphical industry defined in standard EN-12464
- Enabling customer to switch to excellent color rendering properties with low decrease of light level

Features

- High-quality fluorescent coating for excellent color rendering and very accurate color point
- Use of mix of three-band phosphors and halophosphates for high efficacy
- Retrofit in current luminaires for standard TL-D lamps

Application

- Used in applications where excellent color rendering is crucial, such as the graphical industry, printing industry, photo shops, hospitals, etc.


MASTER TL-D 90 Graphica

Versions



G13, T8

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
Graphica 36W/950					
SLV/10					

