



# Product Description

## MASTER TL-D 90 Graphica

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Benefits

- Excellent colour rendering. Making representation of colours extremely realistic
- Lamp developed to answer the needs of the demanding graphical industry (consistent with the strict standards for the graphical industry defined in EN-12464)
- Very accurate colour point
- Attractive packaging configuration
- Direct retrofit for all Standard and Super 80 TL-D lamps operating on conventional or electronic gear
- Choice of daylight and cool daylight colours

### Features

- High-quality fluorescent coating
- Available in two colour designations

### Application

- Used in applications where excellent colour rendering is crucial, such as the graphical industry, printing industry, photo shops, hospitals, etc.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.