



Product Description

MASTER TL-D 90 De Luxe

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Very good colour rendering. Making colours appear rich, deep and enhanced as they do in daylight, making products appear more attractive
- 25% More light than competition
- Enabling customer to switch to 900-colours with (almost) no decrease of light level
- Enabling customers (in certain segments) to respect the new European standard for lighting of indoor workplaces (CEN 12464-1), without investing in new luminaires
- Attractive packaging configuration
- Direct retrofit for all Standard and Super 80 TL-D lamps operating on conventional or HF gear
- Possible to create atmospheres from warm white to cool daylight

Features

- High-quality fluorescent coating
- Available in various colour designations

Application


- Used in applications where good colour rendering is crucial, such as shops (flower, fashion, department, etc.), hairdresser, museums, hospitals, etc

MASTER TL-D 90 De Luxe

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 36W/965 SLV/10	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

