



# For reliable unveiling of secrets

## TL-D Blacklight Blue

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Benefits

- Quick detection of UV-reflecting materials
- Creates special lighting atmospheres and effects

### Features

- Straight outer envelope

### Application

- Detection and analysis in the textile and chemical industries
- Banking and forensic science
- Special effects in night clubs, discos and theatres, and sign lighting


# TL-D Blacklight Blue

## Versions



T26 G13

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/BLACKLIGHT/18	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
BLB LF6PK					

