



# For reliable unveiling of secrets

## TL-D Blacklight Blue

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Benefits

- Quick detection of UV-reflecting materials
- Quick detection of UV-reflecting materials
- Creates special lighting atmospheres and effects
- Creates special lighting atmospheres and effects

### Features

- Straight outer envelope
- Straight outer envelope

### Application

- Detection and analysis in the textile and chemical industries
- Detection and analysis in the textile and chemical industries
- Banking and forensic science
- Banking and forensic science
- Special effects in night clubs, discos and theatres, and sign lighting
- Special effects in night clubs, discos and theatres, and sign lighting

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.