



For reliable unveiling of secrets

TL-D Blacklight Blue

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

优点

- Quick detection of UV-reflecting materials
- Creates special lighting atmospheres and effects

特点

- Straight outer envelope

应用


- Detection and analysis in the textile and chemical industries
- Banking and forensic science
- Special effects in night clubs, discos and theatres, and sign lighting

Versions



TL-D Blacklight Blue

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W BLB 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 18W BLB 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

应用	
汞 (Hg) 含量 (标称)	5.0 mg
基本信息	
底盖	G13
主要应用	Blacklight Blue
照明科技	
颜色代码	108
颜色名称	Blacklight Blue
机械和壳体	
灯泡外形	T26

运营和电气

Order Code	Full Product Name	灯具电流 (标称)	电压 (标称)	功率(额定)(标称)
928048010805	TL-D 18W BLB 1SL/25	0.36 A	59 V	18 W

Order Code	Full Product Name	灯具电流 (标称)	电压 (标称)	功率(额定)(标称)
928048510805	TL-D 36W BLB 1SL/25	0.44 A	103 V	36 W

基本信息

Order Code	Full Product Name	50% 故障条件下的使用寿命 (标称)
928048010805	TL-D 18W BLB 1SL/25	13000 h

Order Code	Full Product Name	50% 故障条件下的使用寿命 (标称)
928048510805	TL-D 36W BLB 1SL/25	15000 h

照明科技

Order Code	Full Product Name	LLMF 2000 小时额定	LLMF 6000 小时额定
928048010805	TL-D 18W BLB 1SL/25	15 %	20 %

Order Code	Full Product Name	LLMF 2000 小时额定	LLMF 6000 小时额定
928048510805	TL-D 36W BLB 1SL/25	10 %	15 %

TL-D Blacklight Blue

