



# Product Description

## MASTER TL-D Xtra

Low-pressure mercury discharge lamp with a tubular 26mm envelope

### Benefits

- Longer lifetime and less early failures lead to less hassle and lower maintenance costs and facilitate the change from spot to group replacement
- Less waste and disposal cost at end-of-life
- Special fluorescent coating gives good colour rendering

### Features

- Significant reduction of early failures based upon a new technology (patent pending)
- Extra long and reliable lifetime
- Highly efficient 3-band fluorescent coating in combination with New Generation pre-coating technology
- Low mercury dose for a long-life lamp
- Fully recyclable lamp technology
- End-cap has an x-shaped green bottom plate to distinguish the lamp from other fluorescent lamps

### Application


- Suitable for use in applications where maintenance costs are high (high ceilings, difficult to reach): department stores, supermarkets, warehouses, production halls, offices and public areas like car parks and railway stations

# MASTER TL-D Xtra

## Versions



## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 58W/840 SLV/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

