



The light source for money checking!

TL Mini Blacklight Blue

This TL Miniature lamp (tube diameter 16 mm) is made of blacklight blue (dark blue) glass, which transmits UV-A radiation, but gives only a minimum of visible light. It is a perfect solution for quick detection of UV-reflecting materials. It is used especially for testing, inspection and analysis in various branches of industry, e.g. criminology, philately and medicine. Furthermore, it is applied to create special effects in the entertainment industry, e.g. in nightclubs and theaters.

Benefits

- Quick detection of UV-reflecting materials
- Creates special lighting atmospheres and effects

Features

- Straight outer envelope

Application

- Detection and analysis in the textile and chemical industries
- Banking and forensic science
- Special effects in night clubs, discos and theatres, and sign lighting


TL Mini Blacklight Blue

Versions



TL Mini Blacklight Blue T5 G5

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 6W BLB 1FM/10X25CC	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

