



# TMS011

## TMS011

An indoor luminaire in single and twin fluorescent lamp versions for general lighting. The range is available with TLD 18W, 36W or 58W lamps for surface-mounted applications. The luminaires can be suspended or direct ceiling mounted. A range of attractive attachments is also available.

### Features

- A high quality luminaire with enhanced safety
- Easy installation and maintenance
- Philips ballast is pre-wired inside the luminaire
- The starter is also provided

### Application

- Discount stores
- Hyper- and supermarkets
- DIY stores
- Convenient stores
- Coves
- Home lighting
- General industries

# TMS011

## Versions



### General Information

Protection class IEC	Safety class I (I)
Lamp family code	TL-D
Optic type	No

## Approval and Application

Order Code	Full Product Name	Ingress protection code
911400857580	TMS011 2xTL-D36W IC	-

Order Code	Full Product Name	Ingress protection code
911400864980	TMS011 1xTL-D18W HFS GMP 220V 50Hz	IP20

## General Information

Order Code	Full Product Name	Compensation circuit	Optical cover/lens type	Gear	Lamp power	Number of light sources
911400857580	TMS011 2xTL-D36W IC	Inductive parallel compensated	No	CONV	36 W	2
911400864980	TMS011 1xTL-D18W HFS GMP 220V 50Hz	-	P	EBS	18 W	1

