



Smart T8 Batten TMS018C – Cool... light your environment in a safe and smart way

Cozy TMS018 C

Our Smart T8 Batten is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

Benefits

- Durable and safe
- Flexible and convenient
- Trendy and professional design

Features

- IEC60598 and CCC-compliant
- Electronic and electromagnetic ballast
- Robust housing
- High-quality lamp holders and connectors
- Emergency-lighting version available

Application

- Car parks
- Corridors
- Industry

Specifications

Cozy TMS018 C

Type	TMS018
Light source	1 or 2 x MASTER TL-D Food / G13 / 18, 30, 36 W
Lamp included	No
Ballast	Electro magnetic (low loss), 220 V / 50 Hz: - Parallel compensated (IC) Electronic, High Frequency 220-240 V / 50-60 Hz: - Electronic (EB)

Ignitor	Series, self-stopping
Optic	Reflector (R)
Connection	SCREW connector
Material	Sheet steel, powder painted
Colour	Housing, reflector: white
Installation	Individual or in-line; screw mounting Through-wiring possible

Versions



TMS018 C TL

Approval and Application

Ingress protection code	IP20
-------------------------	------

Operating and Electrical

Input Voltage	220 V
---------------	-------

General Information

Protection class IEC	Safety class I (I)
Compensation circuit	-
Country version	NO
Gear	EB
Kombipack	-
Lamp family code	TL-D
Lamp power	36 W
Optic type	R

General Information

Order Code	Full Product Name	Number of light sources
910403630717	TMS018 C 1xTL-D36W EB R	1
910403630718	TMS018 C 2xTL-D36W EB R	2

