



Lineco TMS022 – an economical choice

Lineco TMS022 UK

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Výhody

- An economical choice, with a functional surface-mounted batten for 1 or 2 TL-D fluorescent lamps
- Choice of optics for symmetrical or asymmetrical light distribution
- Quick, tool-less installation can be carried out single-handedly

Vlastnosti

- Choice of one or two TL-D fluorescent lamps
- Choice of symmetrical or asymmetrical optics
- Quick, tool-less installation
- Repositionable contact block
- Wide range of snap-on attachments

Aplikace

- Retail
- Industry


Lineco TMS022 UK

Versions

TMS022 - MASTER TL-D - 70 W -
HF Performer - United Kingdom




Rozměrové výkresy




Product

TMS022 2xTL-D58W/840 HFSUK



Product

TMS022 1xTL-D58W/840 HFSUK



Product

GMS022 1/2 58 R-UK

Lineco TMS022 UK

Detaily o výrobku

IPDP_TMS022i_PHL_EN_0003-
Detail photo



Příslušenství

Ordercode 11760799



Application Conditions

Vhodné pro náhodné spínání Není k dispozici

Approval and Application

Kód ochrany proti mechanickým nárazům IK02

IP kód IP20

Operating and Electrical

Vstupní napětí 230 to 240 V

General Information

Značka CE CE mark

Třída ochrany IEC Bezpečnostní třída I

Kompenzační okruh -

Verze pro zemi UK

Nouzové osvětlení No

Značka ENEC ENEC mark

Značka hořlavosti F

Předřadník HFS

Test žhavým drátem Teplota 650 °C, doba 5 s

Kombipack K

Kód řady zdroje TL-D

Příkon zdroje 58 W




Typ optiky No

Kód produktové řady TMS022

General Information

Order Code	Full Product Name	Počet světelných zdrojů
13572400	TMS022 2xTL-D58W/840 HFSUK	2
13575500	TMS022 1xTL-D58W/840 HFSUK	1

Polar Wide Diagrams




IFPS_TMS022 1xTL-D58W HFS +GMS022 R-
 Polar Normal (separate)

IFPS_TMS022 1xTL-D58W HFS +GMS022 R-A-
 Polar Normal (separate)

IFPS_TMS022 1xTL-D58W HFS-Polar Normal
 (separate)

Polar Wide Diagrams



IFPS_TMS022 2xTL-D58W HFS +GMS022 R-
Polar Normal (separate)

