



# e-Batten – easy to install

## T8 e-batten TMS150

The new range of Philips fluorescent electronic battens are lightweight and easy to install thanks to their new cover plate. They're energy-efficient too, providing the perfect solution for virtually any commercial environment. The TMS150 range comes in the usual T8 models. Or you can choose the new TMS151 T5 models for even greater energy savings – up to 20% over standard T8 electronic battens. The new, high-quality European HFP111 programmed-start ballasts ensure superior performance and extended lamp life. The new e-battens can be adapted to a variety of environments using an extensive range of optional attachments that include prismatic diffusers, industrial reflectors and wire guards. Emergency and dimming options are available upon request.

### Benefits

- Energy savings
- Easy to install
- Superior performance and extended lamp life

### Features

- Complies with the latest office-lighting standards
- Latest electronic high-performance ballasts
- Multiple optional accessories for specific tasks

### Application

- Indoor commercial environments

### Specifications

<b>Type</b>	TMS150 (TL-D lamp version)
	TMS151 (TL5 lamp version)
<b>Light source</b>	Fluorescent:
	- 1 or 2 x TL-D / G13 / 18, 36, 58 W
	- 1 or 2 x TL5 / G5 / 14, 28, 35 W
<b>Lamp included</b>	No

<b>Ballast</b>	Electronic, High Frequency 220-240 V / 50-60 Hz:
	- Performer (HFP)
<b>Fused terminal block</b>	Yes
<b>Optical cover</b>	Prismatic (ACP)

## T8 e-batten TMS150

<b>Options</b>	Ballast:	- Integral
	- High Frequency Regulator 1-10 V	
	- High Frequency Regulator TD Dali	
	Emergency lighting:	
	- 1 hour (EL1)	
	- 3 hours (EL3)	
<b>Material</b>		Body: powder-coated steel
		Cover: acrylate
<b>Accessories</b>		Wire guard (ZMS150 WG), optical cover (ZMS150 ACP), industrial reflector (ZMS150 R / ZMS151 R), asymmetric reflector (ZMS150 R-A / ZMS151 R-A)

### Versions



<b>Operating and Electrical</b>	
<b>Input Voltage</b>	220 to 240 V
<b>General Information</b>	
<b>Gear</b>	HFP
<b>Lamp family code</b>	TL5

### General Information

Order Code	Full Product Name	Optical cover/ lens type	Lamp power	Number of light sources
910400966901	TMS151 1xTL5-28W HF-P F 220-240V 50/60Hz	-	28 W	1 pc
910400966903	TMS151 2xTL5-28W HF-P F P 220-240V 50/60	Acrylic cover prismatic	28 W	2 pcs
910400966904	TMS151 2xTL5-35W HF-P F P 220-240V 50/60	Acrylic cover prismatic	35 W	2 pcs

Order Code	Full Product Name	Optical cover/ lens type	Lamp power	Number of light sources
910400966905	TMS151 2xTL5-49W HF-P F P 220-240V 50/60	Acrylic cover prismatic	49 W	2 pcs
910400966910	TMS151 2xTL5-54W HF-P F P 220-240V 50/60	Acrylic cover prismatic	54 W	2 pcs

