



# EcoBAY – Contemporary lighting for areas with high ceilings

## EcoBAY TPK377

EcoBAY is a range of contemporary single luminaires with an MIR04 aluminum reflector, which combines the advantages of TL5 HO fluorescent lamps with high color rendering index (CRI), high luminous flux, and the flexibility to mount traditional HID luminaires. EcoBAY was developed as an option to replace the luminaires that use discharge lamps, for areas with a height of 6 to 9 meters. They are available for four TL5 HO lamps of 50 and 54 W; open and closed versions with polycarbonate diffuser. EcoBAY luminaires are very compact and come fitted with lamps and ballasts. With EcoBAY the owner also reduces energy consumption and maintenance costs.

### Benefits

- Contemporary lighting for areas with high ceilings, using a functional luminaire with TL5 lamps and high efficiency
- Designed especially for general lighting in industrial areas and shops
- High-bay luminaires with four TL5 lamps for ideal color rendering and longer life than HID lamps, minimizing maintenance costs

### Features

- Aluminum-plate reflector MIRO4
- Can be mounted with polycarbonate diffuser
- Suspended or surface-mounted luminaire
- Installation height between 6 and 9 m

Application

- Industrial buildings
- Warehouses
- Schools
- Supermarkets
- Storage areas

Specifications

Type	TPK377
Light source	4 x 50 W / 4 x 54 W TL5
Mains voltage	Electronic 220 V / 50-60 Hz: (EB)
	Electronic Touch&Dim DALI (HFD)
Optical cover	Polycarbonate diffuser

Materials and finishing	White steel-plate fixture
	Aluminum-plate reflector MIRO4 (C-H)
	Polycarbonate diffuser (PC)
Installation	Suspended by means of rods mounted on slabs, ceilings, and tracks

Versions



General Information	
Lamp family code	TL5
Number of light sources	4 pcs
Optic type	High-gloss high reflectance

General Information

Order Code	Full Product Name	Optical cover/lens		Gear	Lamp power
		type			
919106029851	TPK377 4xTL5-54W/840 EB C-H	-		EB	54 W
919106030061	TPK377 4xTL5-54W/840 EB C-H	Polycarbonate bowl/		EB	54 W
	PC	cover			
919106031431	TPK377 4xTL5-50W/840 EB C-H	-		EB	50 W
919106031439	TPK377 4xTL5-50W/840 HFD C-	-		HFD	50 W
	H				

Order Code	Full Product Name	Optical cover/lens		Gear	Lamp power
		type			
919106031441	TPK377 4xTL5-50W/840 EB C-H	Polycarbonate bowl/		EB	50 W
	PC	cover			
919106031449	TPK377 4xTL5-50W/840 HFD C-	Polycarbonate bowl/		HFD	50 W
	H PC	cover			

