



# SmartForm TPS466 – top-class lighting in a fresh, appealing design

## SmartForm TPS466

We all feel and perform better in a pleasant, comfortable working environment. Designed for use in offices, shops and schools, the SmartForm TPS466 family of suspended mounted luminaires combines best-in-class lighting with a clean, distinctive design. These ultra-flat luminaires are available with MASTER TL5 and TL5 ECO lamps in rectangular and square versions with direct/indirect lighting combinations. They can also be used to form light-lines and structures. With its wide choice of very efficient and comfortable micro-optics and covers, SmartForm TPS466 provides the ideal solution for every situation. Lighting controls can be added for further energy saving.

### Benefits

• –

### Features

- Very slim housing – only 47 mm deep
- State-of-the-art lamps
- High-efficiency optics and covers
- Direct/indirect light distribution
- Possibility to add lighting controls

### Application

- Offices
- Shops
- Schools

# SmartForm TPS466

## Specifications

<b>Type</b>	TPS466 (light beam, direct 30% (1 lamp down) indirect 70% (2 lamps up))
<b>Light source</b>	Fluorescent: - 3 x MASTER TL5 ECO / G5 / 25, 32, 45, 50, 73 W - 3 x MASTER TL5 / G5 / 28, 35, 49, 54, 80 W
<b>Lamp included (1 lamp down, 2 lamps up)</b>	Yes, TL5 ECO (830 or 840) Yes, TL5 (lamp color 451 (ActiViva Natural), 452 (ActiViva Active), 827, 830 or 840) No
<b>Ballast (1 ballast down, 1 ballast up)</b>	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency Performer (HFP) - High Frequency Performer, intelligent, multi-watt (HFP-I) - High Frequency Regulator, 1-10 V (HFR) - High Frequency Regulator, DALI (HFD) - High Frequency Regulator DALI, touch & dimming (HFD-T)
<b>Housing configuration (for line arrangements)</b>	Line end, 1 phase (LE1), for ending a line Line feature, 1 phase (LF1), for insertion in a line
<b>Optical cover</b>	OLC micro-lens optic in polycarbonate cover (MLO-PC)
<b>Connection</b>	Push-in connection with pull relief (PIP) Cable, length 200 cm, with plug CEE7 (CCE)
<b>Options</b>	Lighting controls: - Luxsense daylight controller micro (LXM) - ActiLume multi controller (ACL) - ActiLume multi controller wireless (AWL) Internal PVC free wiring (PVCFR) Manual pull switches for up / down (PSW) Euro fuse (FU) included

<b>Materials and color</b>	Housing of powder-coated steel, end-caps of PC-ABS White RAL 9016 based is standard; optional white RAL 9010 or silver grey RAL 9006 based
<b>Installation</b>	Individual or in line; suspended mounting with a suspension set
<b>Accessories</b>	3- lamp luminaire (housing 2- lamp) delivered incl. suspension sets: - ZPS460 SMT1: suspension set single wire, triangel version 1 - ZPS460 SMT2: suspension set single wire, triangel version 2, incl. mains connection - ZPS460 SMTT: suspension set single wire, triangel for T-profile - ZPS460 SMS: suspension set double wires, incl. mains connection Light lines, straight and L-shape to create with ZPS460 CP/CPL coupling pieces; luminaires line-end (LE) and line-feature (LF) are including connection and through-wiring
<b>Remarks</b>	Protection foil to protect the optic during installation
<b>Main applications</b>	Office, education, healthcare, recreation, retail, industry

## Accessories

Optical cover remover

Ordercode 98469599



