



TPS498 X-tend

X-tend TPS498 C

X-tend surface and suspended-mounted luminaires The Philips X-tend family of surface and suspended-mounted luminaires has the perfect combination of cutting-edge technology, functional brilliance and aesthetic appeal. The secret behind X-tend's superb lighting qualities lies in its optic - based on specially designed 3-dimensional curves that offer highly efficient light distribution. X-tend meets most ceiling void restrictions, allowing architects and engineers ultimate design flexibility. TPS498 These range of high-performance luminaires is suitable for TL-D or TL5 fluorescent lamps and a wide range of optics. Optics are supplied with the luminaire on request with a choice of direct, direct/indirect lighting. Optics for asymmetrical lighting can be used in combination with a top mirror for higher performance on request. Straight coupling pieces allow connection of luminaires in a line. There are two different top covers: cover-solid and PC-indirect (D/I version). The luminaire is developed with ease of installation in mind, it can be suspended without removing the optic and lamp during installation.

Features

- Wide selection of best-in-class optics, customized to meet your specific needs
- Choice of fluorescent lamps, TL5 or TL-D, efficiency optimized with TL5 version
- High-quality finishing for a high quality appearance
- Philips V-clip and light weight design, eases installation and maintenance
- Direct/indirect lighting, greater beam control
- Top mirror on request for higher performance
- Pre-fitted optics for quick installation
- Accessories offer flexibility in application

Application

- Office spaces
- Public buildings
- Schools
- Hospitals

Dimensional drawing

TPS498 C

Product	A	B	C	D
TPS498 C 1xTL5-28W/840 HFP D/I M6 FU	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL-D36W HFE D/I C6	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL-D58W HFP D D6 FTB	1540 mm	1638 mm	1560 mm	1580 mm
TPS498 1xTL5-35W/840 HFP D6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL5-35W HFP D/I D6 FTB	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL-D36W HFE D/I D6	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL-D58W HFP D/I M2 FTB	1540 mm	1638 mm	1560 mm	1580 mm
TPS498 C 2xTL5-35W HFE D M6	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL-D58W HFP D/I D6 FTB	1540 mm	1638 mm	1560 mm	1580 mm
TPS498 C 1xTL5-35W/840 HFP D/I D6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL5-28W HFE D M2	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W/840 HFP D/I D6 FU	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W HFE D M6	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-35W/840 HFP M6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 1xTL5-28W/840 HFP D/I D6 FU	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-35W/840 HFP D/I D6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL-D36W HFP D D6 FTB	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL5-28W HFP D M6 FTB	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL-D36W HFP D/I C6	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL-D58W HFP D M2 FTB	1540 mm	1638 mm	1560 mm	1580 mm
TPS498 C 2xTL-D36W HFP D/I M6 FTB	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL5-28W HFP D/I M6	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL-D36W HFP D M6 FTB	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL5-28W HFP D/I M2 FTB	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W HFE D/I M6 FTB	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W HFE D C6	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 1xTL5-35W/840 HFP D/I M6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL5-28W HFE D/I D6 FTB	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL-D58W HFP D/I M6 FTB	1540 mm	1638 mm	1560 mm	1580 mm
TPS498 C 2xTL5-35W/840 HFP D/I M6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL-D36W HFP D/I D6 FTB	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL5-28W HFP D/I D6	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 1xTL5-28W/840 HFP M6 FU	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W HFE D D6	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W HFA D/I M6	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-35W/840 HFP D6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL-D58W HFP D M6 FTB	1540 mm	1638 mm	1560 mm	1580 mm
TPS498 C 2xTL5-28W/840 HFP M6 FU	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W HFE D/I M2 FTB	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 1xTL5-28W/840 HFP D6 FU	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 1xTL5-35W/840 HFP M6 FU	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL-D36W HFE D/I M6	1240 mm	1388 mm	1260 mm	1280 mm
TPS498 C 2xTL5-28W HFE D/I M-D FTB	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W HFE D/I C6 FTB	1188 mm	1286 mm	1208 mm	1228 mm
TPS498 C 2xTL5-28W/840 HFP D6 FU	1188 mm	1286 mm	1208 mm	1228 mm
WRONG CODE!	1488 mm	1620 mm	1508 mm	1528 mm
TPS498 C 2xTL5-28W/840 HFP D/I M6 FU	1188 mm	1286 mm	1208 mm	1228 mm

X-tend TPS498 C

Approval and Application	
Ingress protection code	IP20
General Information	
Gear	EBP
Kombipack	-
Lamp family code	TL5
Lamp power	28
Number of light sources	2
Product Family Code	TPS498
Top reflector	No

General Information

order code	Optic type
911400630380	M6
911400630580	D6
911400636480	M6-A

