



Adreno

T5 Adreno

Philips Adreno electronic fluorescent batten is designed to fit with any home décor perfectly. Its sleek and stylish look makes other battens seem lifeless. And Adreno gives off 11% more light, thanks to the innovative batwing technology, making every corner of your home glow with style. What's more, it uses 20% less energy than your average batten and tube.

Features

- Comfortable natural lamp color
- Unique cold chamber technology
- Unique 3D batwing profile for maximum light output
- Easy installation
- Flicker-free with instant start electronic operation
- Light weight and slim
- Long lasting lifespan
- Up to 20% savings in energy with TL-8 lamps

Application

- Living rooms
- Bedrooms
- Kitchen
- Washrooms

T5 Adreno

Versions




TWG128c batten

Dimensional drawing


TWG128 C

Product	A
TWG128 C 1xTL5-14W/840 HF 220-240V CUL2	
TWG128 C 1xTL5-28W CCE2	
TWG128 C 1xTL5-14W/840 HF 110-140V CUL2	
TWG128 C 1xTL5-28W CUL	
TWG128 C 1xTL5-28W/830 HF CBS	
TWG128 C 1xTL5-14W/840 HF 110-140V CCE2	
TWG128 C 1xTL5-28W/840 HF 110-140V CUL2	
TWG128 C 1xTL5-28W/865	
TWG128 C 1xTL5-28W/830 HF 220V P CCN2	
TWG128 C 1xTL5-28W P CBS	
TWG128 C 1xTL5-28W P CBS	
TWG128 C 1xTL5-28W P CCE2	
TWG128 C 1xTL5-28W/840 HF P CKP2	
TWG128 C 1xTL5-28W/830 HF 220V P CCN2	
TWG128 C 1xTL5-14W/840 HF 220-240V CCE2	
TWG128 C 1xTL5-28W/830 HF CKP2	
TWG128 C 1xTL5-28W CBS	
TWG128/2005 TL5-28W/830 HF P CCE2	
TWG128 C 1xTL5-28W/830 HF P CBS	
TWG128 C 1xTL5-28W	
TWG128 C 1xTL5-28W CUL	
TWG128 C 1xTL5-28W/840 HF 220-240V CUL2	
TWG128 C 1xTL5-28W/865 AU	
TWG128 C 1xTL5-28W/830 HF 240V P CAU2	
TWG128 C 1xTL5-28W CCE2	
TWG128 C 1xTL5-28W P CUL	
TWG128 C 1xTL5-28W/865	
TWG128 C 1xTL5-28W/840 HF 220-240V CKP2	
TWG128 C 1xTL5-28W P CCE2	
TWG128 C 1xTL5-28W P CUL	
TWG128 C 1xTL5-28W/840 HF	
TWG128 C 1xTL5-28W/840	
TWG128 C 1xTL5-28W/830 HF 240V CAU2	
TWG128 C 1xTL5-28W/830 HF P CKP2	
TWG128 C 1xTL5-28W/865 HF 220-240V CKP2	
TWG128 C 1xTL5-28W/830 HF CCE2	
TWG128 C 1xTL5-28W/865 P AU	
TWG128 C 1xTL5-28W/840 HF 110-140V CCE2	
TWG128 C 1xTL5-28W/840 AU	
TWG128 C 1xTL5-28W/840 P AU	
TWG128 C 1xTL5-28W CBS	
TWG128 C 1xTL5-28W/840 HF 220-240V CCE2	
TWG128 C 1xTL5-28W/865 HF P CKP2	

Dimensional drawing




TWG128 C




TWG128 C

TWG128 C

Product details



Interlinking cables



Ultra-slim batten

T5 Adreno

Approval and Application	
Ingress protection code	IP20
Operating and Electrical	
Input Voltage	220 to 240
General Information	
Protection class IEC	Safety class II (II)
Country version	NO
Optical cover/lens type	No
Gear	HF
Lamp family code	TL5
Number of light sources	1
Product Family Code	TWG128

General Information

order code	Lamp power
18012099	14
18013799	21
18014499	28

