




Adreno

T5 Adreno

Philips Adreno electronic fluorescent batten is designed to fit with any home décor perfectly. Its sleek and stylish look makes other battens seem lifeless. And Adreno gives off 11% more light, thanks to the innovative batwing technology, making every corner of your home glow with style. What's more, it uses 20% less energy than your average batten and tube.

Features

- Comfortable natural lamp color
- Unique cold chamber technology
- Unique 3D batwing profile for maximum light output
- Easy installation
- Flicker-free with instant start electronic operation
- Light weight and slim
- Long lasting lifespan
- Up to 20% savings in energy with TL-8 lamps

Application

- Living rooms
- Bedrooms
- Kitchen
- Washrooms

T5 Adreno

Versions



TWG121c batten



TWG114c batten

Dimensional drawing

TWG114 C


Product	A
TWG114 C 1xTL5-14W P CCE2	605 mm
TWG114 C 1xTL5-21W/830 EI 240V P CAU2	905 mm
TWG114 C 1xTL5-14W P CUL	605 mm
TWG114 C 1xTL5-14W/830 EI 220V P CCN2	605 mm
TWG114 C 1xTL5-14W/865 P AU	605 mm
TWG114 C 1xTL5-14W/840 P AU	605 mm
TWG114 C 1xTL5-14W/830 EI P CKP2	605 mm
TWG114 C 1xTL5-14W P CCE2	605 mm
TWG114 C 1xTL5-14W P CUL	605 mm
TWG114 C 1xTL5-14W/865 EI P CKP2	605 mm
TWG114 C 1xTL5-14W/830 EI P CBS	605 mm
TWG114 C 1xTL5-14W/865 P IN	605 mm
TWG114 C 1xTL5-14W P CBS	605 mm
TWG114 C 1xTL5-14W	605 mm
TWG114 C 1xTL5-14W/840 EI P CKP2	605 mm
TWG114 C 1xTL5-14W/840	605 mm
TWG114 C 1xTL5-14W/830 EI P CCE2	605 mm

TWG128 C

Product	A
TWG128 C 1xTL5-14W/840 HF 220-240V CUL2	605 mm
TWG128 C 1xTL5-28W CCE2	1205 mm
TWG128 C 1xTL5-14W/840 HF 110-140V CUL2	605 mm
TWG128 C 1xTL5-28W CUL	1205 mm
TWG128 C 1xTL5-28W/830 HF CBS	1205 mm
TWG128 C 1xTL5-14W/840 HF 110-140V CCE2	605 mm
TWG128 C 1xTL5-28W/840 HF 110-140V CUL2	1205 mm
TWG128 C 1xTL5-28W/865	1205 mm
TWG128 C 1xTL5-28W/830 HF 220V P CCN2	1205 mm
TWG128 C 1xTL5-28W P CBS	1205 mm
TWG128 C 1xTL5-28W P CBS	1205 mm
TWG128 C 1xTL5-28W P CCE2	1205 mm
TWG128 C 1xTL5-28W/840 HF P CKP2	1205 mm
TWG128 C 1xTL5-28W/830 HF 220V P CCN2	1205 mm
TWG128 C 1xTL5-14W/840 HF 220-240V CCE2	605 mm
TWG128 C 1xTL5-28W/830 HF CKP2	1205 mm
TWG128 C 1xTL5-28W CBS	1205 mm
TWG128/2005 TL5-28W/830 HF P CCE2	905 mm
TWG128 C 1xTL5-28W/830 HF P CBS	1205 mm
TWG128 C 1xTL5-28W	1205 mm
TWG128 C 1xTL5-28W CUL	1205 mm
TWG128 C 1xTL5-28W/840 HF 220-240V CUL2	1205 mm
TWG128 C 1xTL5-28W/865 AU	1205 mm
TWG128 C 1xTL5-28W/830 HF 240V P CAU2	1205 mm
TWG128 C 1xTL5-28W CCE2	1205 mm
TWG128 C 1xTL5-28W P CUL	1205 mm
TWG128 C 1xTL5-28W/865	1205 mm
TWG128 C 1xTL5-28W/840 HF 220-240V CKP2	1205 mm
TWG128 C 1xTL5-28W P CCE2	1205 mm
TWG128 C 1xTL5-28W P CUL	1205 mm

Dimensional drawing

TWG121 C



TWG114 C


Product	A
TWG128 C 1xTL5-28W/840 HF	1205 mm
TWG128 C 1xTL5-28W/840	1205 mm
TWG128 C 1xTL5-28W/830 HF 240V CAU2	1205 mm
TWG128 C 1xTL5-28W/830 HF P CKP2	1205 mm
TWG128 C 1xTL5-28W/865 HF 220-240V CKP2	1205 mm
TWG128 C 1xTL5-28W/830 HF CCE2	1205 mm
TWG128 C 1xTL5-28W/865 P AU	1205 mm
TWG128 C 1xTL5-28W/840 HF 110-140V CCE2	1205 mm
TWG128 C 1xTL5-28W/840 AU	1205 mm
TWG128 C 1xTL5-28W/840 P AU	1205 mm
TWG128 C 1xTL5-28W CBS	1205 mm
TWG128 C 1xTL5-28W/840 HF 220-240V CCE2	1205 mm
TWG128 C 1xTL5-28W/865 HF P CKP2	1205 mm

Product	A
TWG121 C 1xTL5-21W/830 EI P CCE2	905 mm
TWG121 C 1xTL5-21W/840 EI P CKP2	905 mm
TWG121 C 1xTL5-21W P CUL	905 mm
TWG121 C 1xTL5-21W/830 EI P CKP2	905 mm
TWG121 C 1xTL5-21W/865	905 mm
TWG121 C 1xTL5-21W P CUL	905 mm
TWG121 C 1xTL5-21W/830 EI 220V P CCN2	905 mm
TWG121 C 1xTL5-21W P CBS	905 mm
TWG121 C 1xTL5-21W P CBS	905 mm
TWG121 C 1xTL5-21W/865 EI P CKP2	905 mm
TWG121 C 1xTL5-21W/830 EI P CBS	905 mm
TWG121 C 1xTL5-21W/830 EI 220V P CAU2	905 mm
TWG121 C 1xTL5-21W/840	905 mm
TWG121 C 1xTL5-21W/865 P AU	905 mm
TWG121 C 1xTL5-21W P CCE2	905 mm
TWG121 C 1xTL5-21W/840 P AU	905 mm
TWG121 C 1xTL5-21W P CCE2	905 mm

TWG128 C

T5 Adreno


Dimensional drawing




TWG121 C

TWG128 C


Product details




Interlinking cables



Ultra-slim batten



Interlinking cables



Ultra-slim batten

Approval and Application	
Ingress protection code	IP20
General Information	
Protection class IEC	Safety class II
Lamp family code	TL5
Number of light sources	1 pc

Operating and Electrical

order code	Input Voltage
911401120780	220 to 240

order code	Input Voltage
911401120880	220 to 240

T5 Adreno

order code	Input Voltage
911401120980	220 to 240
911401121480	220 to 240
911401125680	220 to 240
911401126680	220 to 240
911401127080	220 to 240
911401127180	220 to 240
911401130780	220 to 240
911401131580	220
911401132380	220 to 240
911401132480	220 to 240
911401121080	220 to 240
911401121180	220 to 240

order code	Input Voltage
911401124680	220 to 240
911401125180	220 to 240
911401130680	220 to 240
911401131480	220
911401132280	220 to 240
911401121280	220 to 240
911401121380	220 to 240
911401123680	220 to 240
911401124180	220 to 240
911401130580	220 to 240
911401131380	220
911401132180	220 to 240

General Information

order code	Country	Optical cover/lens		Product Family	
	version	type	Gear	Lamp power	Code
911401120780	NO	-	HF	28	-
911401120880	NO	-	HF	28	-
911401120980	NO	-	HF	28	TWG128
911401121480	NO	-	HF	28	TWG128
911401125680	NO	-	HF	28	TWG128
911401126680	NO	Prismatic refractor	HF	28	TWG128
911401127080	AU	Prismatic refractor	HF	28	TWG128
911401127180	NO	Prismatic refractor	HF	28	TWG128
911401130780	NO	Prismatic refractor	HF	28	TWG128
911401131580	NO	Prismatic refractor	HF	28	TWG128
911401132380	NO	Prismatic refractor	HF	21	-
911401132480	NO	-	HF	28	TWG128
911401121080	NO	-	EI	21	TWG121

order code	Country	Optical cover/lens		Product Family	
	version	type	Gear	Lamp power	Code
911401121180	NO	-	EI	21	TWG121
911401124680	NO	Prismatic refractor	EI	21	TWG121
911401125180	NO	Prismatic refractor	EI	21	-
911401130680	NO	Prismatic refractor	EI	21	TWG121
911401131480	NO	Prismatic refractor	EI	21	-
911401132280	NO	Prismatic refractor	EI	21	TWG121
911401121280	NO	-	EI	14	TWG114
911401121380	NO	-	EI	14	-
911401123680	NO	Prismatic refractor	EI	14	TWG114
911401124180	NO	Prismatic refractor	EI	14	TWG114
911401130580	NO	Prismatic refractor	EI	14	TWG114
911401131380	NO	Prismatic refractor	EI	14	TWG114
911401132180	NO	Prismatic refractor	EI	14	TWG114

