



High-performance ballasts for residential and commercial applications

AmbiStar

Ambistar electronic ballasts are an easy-to-install, energy-efficient replacement solution for optimizing residential and hospitality lighting.

Benefits

- Compliant with California Title 24 and DOE efficiency requirements
- Quick, flicker-free starting
- Easy to install in existing fixtures

Features

- FCC Class B EMI Rating, an EPA Energy Star requirement
- Efficient electronic circuitry
- Lamp ignition in less than 1 second
- Standard mounting footprints


Application

- Residential
- Hospitality

Versions



Dimensional drawing



| Product | A1 | A2 | B1 | C1 |
|----------------------|--------|--------|--------|--------|
| AMBISTAR REB2P32N35M | 9.5 in | 8.9 in | 1.3 in | 1.0 in |

