



# High-performance ballasts for residential and commercial applications

## AmbiStar

Ambistar electronic ballasts are an easy-to-install, energy-efficient replacement solution for optimizing residential and hospitality lighting.

### Benefits

- Compliant with California Title 24 and DOE efficiency requirements
- Quick, flicker-free starting
- Easy to install in existing fixtures

### Features

- FCC Class B EMI Rating, an EPA Energy Star requirement
- Efficient electronic circuitry
- Lamp ignition in less than 1 second
- Standard mounting footprints

### Application

- Residential
- Hospitality


Versions



RELB2S40N35I

REB4P32SC35M

Dimensional drawing



Product	A1	A2	B1	C1
AMBISTAR ELE BALLAST (2) F32T8 120V	9.5 in	8.9 in	1.3 in	1.0 in
AMBISTAR ELE BALLAST (2) F40T12 120V	9.50 in	8.90 in	1.30 in	1.00 in
AMBISTAR ELE BALLAST (4) F32T8 120V	9.5 in	8.90 in	1.7 in	1.18 in
AMBISTAR ELE BALLAST (2) F40T12 120V	9.50 in	8.90 in	1.30 in	1.00 in

Operating and Electrical	
Input Frequency	60 Hz
Input Voltage	120 V

Operating and Electrical

Order Code	Full Product Name	Total Harmonic Distortion
		USA
RELB2S40N35I	AMBISTAR ELE BALLAST (2) F40T12 120V	20 %
RELB2S40N35M	AMBISTAR ELE BALLAST (2) F40T12 120V	20 %

Order Code	Full Product Name	Total Harmonic Distortion
		USA
REB2P32N35M	AMBISTAR ELE BALLAST (2) F32T8 120V	150 %
REB4P32SC35M	AMBISTAR ELE BALLAST (4) F32T8 120V	125 %

General Information

Order Code	Full Product Name	Number Of Lamps	Lamp Type
RELB2S40N35I	AMBISTAR ELE BALLAST (2) F40T12 120V	1/2 piece/unit	F40T12
RELB2S40N35M	AMBISTAR ELE BALLAST (2) F40T12 120V	1/2 piece/unit	F40T12

Order Code	Full Product Name	Number Of Lamps	Lamp Type
REB2P32N35M	AMBISTAR ELE BALLAST (2) F32T8 120V	1/2 piece/unit	F32T8
REB4P32SC35M	AMBISTAR ELE BALLAST (4) F32T8 120V	3/4 piece/unit	F32T8

Mechanical and Housing

Order Code	Full Product Name	Housing
RELB2S40N35I	AMBISTAR ELE BALLAST (2) F40T12 120V	N
RELB2S40N35M	AMBISTAR ELE BALLAST (2) F40T12 120V	N

Order Code	Full Product Name	Housing
REB2P32N35M	AMBISTAR ELE BALLAST (2) F32T8 120V	N
REB4P32SC35M	AMBISTAR ELE BALLAST (4) F32T8 120V	SC

