



The right fit for your high-output applications.

Centium T12HO

No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.

Benefits

- IntelliVolt versions now available, 1/2-lamp operation of 8' 95/110W T12 slimline lamps
- Improved efficiency over magnetic counterparts
- Lighter weight with the same mounting and wiring configuration

Features

- IntelliVolt (120-277V) input voltage range
- 1 or 2 Lamp operation

Application

- Retail, commercial, institutional and industrial applications including; schools, offices, specialty & department stores, warehouses and manufacturing


Centium T12HO

Versions



ICN2S110SC35I

Dimensional drawing



Product	A1	A2	B1	C1
CENTIUM ICN2S110SC35I	9.5 in	8.90 in	1.7 in	1.18 in
CENTIUM ICN2S110SC35M	9.5 in	8.90 in	1.7 in	1.18 in

