



# High Efficiency

## Optanium T5

Optanium ballasts for T5 lamps are part of our effort to promote environmental responsibility through Smart Solutions – energy efficient products, lighting systems, services and expertise through Philips Advance branded products.

### Benefits

- High efficiency design
- Maximize energy savings with improved ballast efficiency

### Features

- IntelliVolt Technology (120–277V)
- Lamp EOL Protection
- UL Type CC rated – Anti-arcing circuitry provides greater flexibility to meet end-user application requirements

### Application

- Retail, commercial, institutional and industrial applications including; schools, offices, specialty & department stores, warehouses and manufacturing


### Versions



IOP2S28115SC35M

# Optanium T5

## Dimensional drawing



Product	A1	A2	B1	C1
OPTANIUM ELE BALLAST (2) F28T5 120-277V	9.5 in	8.90 in	1.7 in	1.18 in
OPTANIUM ELE BALLAST (2) F28T5 120-277V	9.5 in	8.90 in	1.7 in	1.18 in

