



High Efficiency

Optanium T5

Optanium ballasts for T5 lamps are part of our effort to promote environmental responsibility through Smart Solutions – energy efficient products, lighting systems, services and expertise through Philips Advance branded products.

Benefits

- High efficiency design
- Maximize energy savings with improved ballast efficiency

Features

- IntelliVolt Technology (120–277V)
- Lamp EOL Protection
- UL Type CC rated – Anti-arcing circuitry provides greater flexibility to meet end-user application requirements

Application

- Retail, commercial, institutional and industrial applications including; schools, offices, specialty & department stores, warehouses and manufacturing


Versions



IOP2S28115SC35M

Optanium T5

Dimensional drawing



Product	A1	A2	B1	C1
OPTANIUM IOP2S2895SC35M	9.5 in	8.90 in	1.7 in	1.18 in
OPTANIUM IOP2S28115SC35M	9.5 in	8.90 in	1.7 in	1.18 in

