



Compact designs, unlimited possibilities

e-Vision Low Wattage 20-150W

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

优点

- Constant lamp wattage for optimal color control and maximum performance
- Significant energy savings can be achieved when compared to incandescent or magnetic alternatives

特点

- Low frequency lamp operation
- Intellivolt 120-277V input range
- Metallic enclosures for optimal thermal dissipation
- Smaller and lighter weight than magnetic HID ballasts
- Thermally protected, internally fused, and output short circuit protected with Lamp End-of-Life shutdown

应用


- Retail display and accent lighting in both track and downlights, lobbies, atriums, landscape and façade lighting

e-Vision Low Wattage 20-150W

Versions



二维绘图



| Product | A1 | A2 | A3 | A4 | A5 | B1 | B2 | C1 |
|---------------------|--------|--------|--------|--------|---------|--------|--------|--------|
| E-VISION IMH39GBLSM | 3.8 in | 3.5 in | 3.4 in | 2.0 in | 1.13 in | 3.0 in | 2.6 in | 1.2 in |
| E-VISION IMH70GLFM | 3.8 in | 3.5 in | 3.4 in | 2.0 in | 1.13 in | 3.0 in | 2.6 in | 1.2 in |

| 运营和电气 | |
|---------|--------------|
| 输入频率 | 50 至 60 岁 Hz |
| 输入电压 | 120-277 V |
| 美国总谐波变形 | 15 % |
| 基本信息 | |
| 灯具数量 | 1 件/单位 |
| 机械和壳体 | |
| 外壳 | G |

基本信息

| Order Code | Full Product Name | 灯具类型 |
|--------------|--|--------|
| 913710259402 | E-VISION ELE MH BAL 39W M130 120-277 50/60HZ | 39W MH |

| Order Code | Full Product Name | 灯具类型 |
|--------------|---|--------|
| 913710259802 | E-VISION ELE MH BAL 70W M139/M143 120-277 50/60HZ | 70W MH |

e-Vision Low Wattage 20-150W

