



The next generation of white light

e-Vision Medium Wattage 210-315W

Pairing Philips Advance e-Vision ballasts with Philips MasterColor Elite Medium Wattage lamps provides a powerful combination of sparkling, white light and energy efficiency superior to what other lighting technologies can offer.

Avantages

- Significant upgrade opportunity over traditional HID systems
- Viable alternative to fluorescent options
- Excellent color quality and consistent light output from beginning to end

Fonctions

- IntelliVolt 200-277V input with 92% efficiency
- Dimming to 50% of lamp power
- Metallic Enclosure for optimal thermal dissipation

Application


- Indoor High-bay, flood and recessed fixtures in retail, institutional and industrial applications

e-Vision Medium Wattage 210-315W

Versions



Schéma dimensionnel



Product	A1	A2	A3	B1	B2	C1
MASTERCOLOR ELITE MEDIUM WATTAGE HZTMH210315RLFM	8,20 in	7,60 in	7,50 in	4,90 in	3,40 in	2,20 in
MASTERCOLOR ELITE MEDIUM WATTAGE IZTMH210315RLFM	8,2 in	7,6 in	7,5 in	4,9 in	3,4 in	2,2 in



e-Vision Medium Wattage 210-315W

Fonctionnement et électricité

Fréquence d'entrée 50 à 60 Hz

Distorsion harmonique totale États-Unis 15 %

Renseignements généraux

Nombre de lampes 1 pièce/unit

Type de lampe 315W Philips CDM
Elite

Mécanique et boîtier

Boîtier R

Caractéristiques du système

Puissance nominale ballast-lampe 315 W

Fonctionnement et électricité

Order Code	Full Product Name	Tension d'entrée	Order Code	Full Product Name	Tension d'entrée
516856	MASTERCOLOR ELITE MEDIUM WATTAGE ELE MH BAL 210/315W PS 347-480V	347-480 V	197954	MASTERCOLOR ELITE MEDIUM WATTAGE ELE MH BAL 210/315W PS 200-277V	200-277 V

