



# Appropriate choice for many linear fluorescent lamp types on the market

## Mark III

Available for many linear fluorescent lamp types sold today, including Rapid Start, Slimline, High Output and Very High Output. Magnetic ballasts can be used in any application where these lamps are used.

### Benefits

- 60 HZ lamp operation eliminates possible EMI/RFI interference

### Features

- Provides energy savings for linear fluorescent lamps versus standard magnetic

### Application

- General office, warehouses, gymnasiums, manufacturing facilities, parking garages


Mark III

Versions



G2S110TPM

Dimensional drawing



Product	A1	A2	B1	C1
MARK III MAG BALLAST (2) F96T12/HO 347V	11.75 in	11.14 in	3.19 in	2.63 in

