



# Get your city ready for the future with DigiStreet

## DigiStreet

Developed with the aim to become your long term partner, the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the Philips CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

### Benefits

- Prepared for the future, it is easy to upgrade directly after installation or later with future CMS nodes and sensors to enable new functionalities
- Large availability of lense optics to match international road and street geometries
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information


**Features**

- Easy luminaire identification due to the Philips Service tag
- High efficacy up to 161 lm/W
- Choice of 30+ different beams and different internal louvers
- Surge protection, 10 kV
- L-tune tool available
- Lifetime 100Khrs up to L96 at Tq +25 °C
- Internal louver (optional)

**Application**

- Traffic routes and main access road
- Urban and residential area
- City centers and main streets
- Cycle paths, footpaths and pedestrian crossings

**Dimensional drawing**



Product details

Digistreet-BGP760-DP06.tif



Digistreet-BGP760-DP09.tif



Digistreet-BGP760-DP10.tif



Digistreet-BGP760-DP11.tif




Digistreet-BGP761-DP17.tif



Digistreet-BGP761-DP18.tif



Digistreet-BGP761-DP19.tif



Digistreet-BGP761-DP20.tif



## Product details



Digistreet-BGP761-DP21.tif



Digistreet-BGP761-DP22.tif



Digistreet-BGP761-DP23.tif



Digistreet-BGP761-DP24.tif



Digistreet-BGP761-DP25.tif



Digistreet-BGP761-DP26.tif

### General Information

CE mark	Yes
Driver included	Yes
Flammability mark	-
Light source replaceable	Yes

### Light Technical

Optical cover type	Flat glass
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0

### Approval and Application

Mech. impact protection code	IK09
Ingress protection code	IP66

### General Information (1/2)

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	-	-	LED95	1 unit
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	-	-	LED95	1 unit
910925866220	BGP762 LED120-~/830 II DN11 DGR D11 76	-	-	LED120	1 unit
910925866221	BGP762 LED159-~/830 II DM70 DGR DDF27 D18	-	-	LED159	1 unit
910925866222	BGP762 LED129-~/740 I DM11 DGR 32-48	-	-	LED129	1 unit
910925866223	BGP762 LED169-~/740 I DS50 DGR 62	-	-	LED169	1 unit

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	-	-	LED110	1 unit
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	-	-	LED149	1 unit
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	-	-	LED180	1 unit
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	-	-	LED100	1 unit
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	-	-	LED139	1 unit
910925866229	BGP762 LED170-/830 II DW10 DGR 76	-	-	LED170	1 unit
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	-	-	LED95	1 unit
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	-	-	LED169	1 unit
910925866245	BGP762 LED200-/740 I DW50 DGR 62	-	-	LED200	1 unit
910925866246	BGP762 LED210-/740 II DX70 DGR 76	-	-	LED210	1 unit
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	-	-	LED190	1 unit
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	-	-	LED220	1 unit
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	-	-	LED120	1 unit
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	-	-	LED159	1 unit
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	-	-	LED239	1 unit
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	-	-	LED220	1 unit
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	-	-	LED239	1 unit
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	-	-	LED239	1 unit
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	-	-	LED149	1 unit
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	-	-	LED239	1 unit
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	EB	Temperature 650 °C, duration 5 s	LED10	1 unit
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	EB	Temperature 650 °C, duration 5 s	LED12	1 unit
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	EB	Temperature 650 °C, duration 5 s	LED14	1 unit
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	EB	Temperature 650 °C, duration 5 s	LED16	1 unit
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	EB	Temperature 650 °C, duration 5 s	LED22	1 unit
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	EB	Temperature 650 °C, duration 5 s	LED24	1 unit
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	EB	Temperature 650 °C, duration 5 s	LED27	1 unit

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
910925863563	BGP760 LED30-/830 II DW10 DGR 62	EB	Temperature 650 °C, duration 5 s	LED30	1 unit
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	EB	Temperature 650 °C, duration 5 s	LED34	1 unit
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	EB	Temperature 650 °C, duration 5 s	LED44	1 unit
910925863567	BGP760 LED49-/740 II DX70 DGR 62	EB	Temperature 650 °C, duration 5 s	LED49	1 unit
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	-	-	LED24	1 unit
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	-	-	LED44	1 unit
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	-	-	LED16	1 unit
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	-	-	LED16	1 unit
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	-	-	LED60	1 unit
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	-	-	LED60	1 unit
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	-	-	LED60	1 unit
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	-	-	LED49	1 unit
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	-	-	LED49	1 unit
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	-	-	LED280	2 units
910925866249	BGP763 LED300-/740 I DW50 DGR 62	-	-	LED300	2 units
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	-	-	LED260	2 units
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	-	-	LED340	2 units
910925866253	BGP763 LED320-/740 II DX70 DGR 76	-	-	LED320	2 units
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	-	-	LED260	2 units
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	-	-	LED360	2 units
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	-	-	LED340	2 units
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	-	-	LED360	2 units
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	-	-	LED360	2 units
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	-	-	LED45	1 unit
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	-	-	LED45	1 unit
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	-	-	LED45	1 unit
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	-	-	LED74	1 unit

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	-	-	LED94	1 unit
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	-	-	LED109	1 unit
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	-	-	LED55	1 unit
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	-	-	LED84	1 unit
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	-	-	LED55	1 unit
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	-	-	LED84	1 unit
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	-	-	LED50	1 unit
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-	-	LED79	1 unit
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	-	-	LED59	1 unit
910925866241	BGP761 LED90-/740 II DW10 DGR 62	-	-	LED90	1 unit
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	-	-	LED74	1 unit
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	-	-	LED84	1 unit
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	-	-	LED119	1 unit
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	-	-	LED119	1 unit
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	-	-	LED84	1 unit

General Information (2/2)

Order Code	Full Product Name	Product family code	Service tag	Order Code	Full Product Name	Product family code	Service tag
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	BGP762	Yes	910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	BGP762	-
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	BGP762	Yes	910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	BGP762	-
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	BGP762	-	910925866492	BGP762 LED120/740 I DM10 DGR 62 S	BGP762	Yes
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	BGP762	-	910925866493	BGP762 LED159/740 I DM10 DGR 62 S	BGP762	Yes
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	BGP762	-	910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	BGP762	Yes
910925866223	BGP762 LED169-/740 I DS50 DGR 62	BGP762	-	910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	BGP762	Yes
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	BGP762	-	910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	BGP762	Yes
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	BGP762	-	910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	BGP762	Yes
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	BGP762	-	910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	BGP762	Yes
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	BGP762	-	910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	BGP762	Yes
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	BGP762	-	910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	BGP760	-
910925866229	BGP762 LED170-/830 II DW10 DGR 76	BGP762	-				
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	BGP762	-				
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	BGP762	-				
910925866245	BGP762 LED200-/740 I DW50 DGR 62	BGP762	-				
910925866246	BGP762 LED210-/740 II DX70 DGR 76	BGP762	-				

Order Code	Full Product Name	Product	
		family code	Service tag
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	BGP760	-
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	BGP760	-
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	BGP760	-
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	BGP760	-
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	BGP760	-
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	BGP760	-
910925863563	BGP760 LED30-/830 II DW10 DGR 62	BGP760	-
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	BGP760	-
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	BGP760	-
910925863567	BGP760 LED49-/740 II DX70 DGR 62	BGP760	-
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	BGP760	-
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	BGP760	-
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	BGP760	Yes
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	BGP760	Yes
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	BGP760	Yes
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	BGP760	Yes
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	BGP760	Yes
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	BGP760	Yes
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	BGP760	Yes
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	BGP763	-
910925866249	BGP763 LED300-/740 I DW50 DGR 62	BGP763	-
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	BGP763	-
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	BGP763	-

Order Code	Full Product Name	Product	
		family code	Service tag
910925866253	BGP763 LED320-/740 II DX70 DGR 76	BGP763	-
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	BGP763	Yes
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	BGP763	Yes
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	BGP763	Yes
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	BGP763	Yes
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	BGP763	Yes
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	BGP761	Yes
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	BGP761	Yes
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	BGP761	-
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	BGP761	-
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	BGP761	-
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	BGP761	-
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	BGP761	-
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	BGP761	-
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	BGP761	-
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	BGP761	-
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	BGP761	-
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	BGP761	-
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	BGP761	-
910925866241	BGP761 LED90-/740 II DW10 DGR 62	BGP761	-
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	BGP761	-
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	BGP761	Yes
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	BGP761	Yes
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	BGP761	Yes
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	BGP761	Yes

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color	Color rendering
				Temperature (Nom)	index (CRI)
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	160° - 42° x 53°	518 ClearStar WW	1800 K	50
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	160° - 42° x 53°	420 ClearStar NW	2000 K	40
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	53° x 71°	830 warm white	3000 K	80
910925866221	BGP762 LED159-/830 II	-	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color	Color rendering
				Temperature (Nom)	index (CRI)
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	160° - 42° x 54°	740 neutral white	4000 K	70
910925866223	BGP762 LED169-/740 I DS50 DGR 62	32° x 29°	740 neutral white	4000 K	70
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	68° x 158°	740 neutral white	4000 K	70



Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925866229	BGP762 LED170-/830 II DW10 DGR 76	61° x 150°	830 warm white	3000 K	80
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	157° - 33° x 55°	740 neutral white	4000 K	70
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	30°	740 neutral white	4000 K	70
910925866245	BGP762 LED200-/740 I DW50 DGR 62	152° - 24° x 66°	740 neutral white	4000 K	70
910925866246	BGP762 LED210-/740 II DX70 DGR 76	106° x 86°	740 neutral white	4000 K	70
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	149° - 10° x 57°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	152° - 25° x 66°	740 neutral white	4000 K	70
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	151° - 43° x 67°	740 neutral white	4000 K	70
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	152° - 25° x 66°	740 neutral white	4000 K	70
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	149° - 10° x 57°	740 neutral white	4000 K	70
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	149° - 10° x 57°	740 neutral white	4000 K	70
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	157° - 33° x 55°	740 neutral white	4000 K	70
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	68° x 157°	740 neutral white	4000 K	70
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	53° x 71°	830 warm white	3000 K	80
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	-	830 warm white	3000 K	80
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	32° x 29°	740 neutral white	4000 K	70
910925863563	BGP760 LED30-/830 II DW10 DGR 62	61° x 150°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	152° - 24° x 66°	740 neutral white	4000 K	70
910925863567	BGP760 LED49-/740 II DX70 DGR 62	106° x 44°	740 neutral white	4000 K	70
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	160° - 42° x 53°	518 ClearStar WW	1800 K	50
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	160° - 42° x 53°	420 ClearStar NW	2000 K	40
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	151° - 43° x 67°	740 neutral white	4000 K	70
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	152° - 25° x 66°	740 neutral white	4000 K	70
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	149° - 10° x 57°	740 neutral white	4000 K	70
910925867995	BGP760 LED- HB/740 II DM32 DGR MSP CLO D1	149° - 10° x 57°	740 neutral white	4000 K	70
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	61° x 150°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866249	BGP763 LED300-/740 I DW50 DGR 62	152° - 24° x 66°	740 neutral white	4000 K	70
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
910925866253	BGP763 LED320-/740 II DX70 DGR 76	106° x 44°	740 neutral white	4000 K	70
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	152° - 25° x 66°	740 neutral white	4000 K	70
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	151° - 43° x 67°	740 neutral white	4000 K	70
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	152° - 25° x 66°	740 neutral white	4000 K	70
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	160° - 42° x 53°	518 ClearStar WW	1800 K	50
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	160° - 42° x 53°	420 ClearStar NW	2000 K	40
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	157° - 33° x 55°	740 neutral white	4000 K	70
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	157° - 33° x 55°	740 neutral white	4000 K	70
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	68° x 157°	740 neutral white	4000 K	70
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	32° x 29°	740 neutral white	4000 K	70
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	160° - 42° x 54°	740 neutral white	4000 K	70
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925866239	BGP761 LED79-/830 II	-	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
	DM70 DGR DDF27 D18				
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	53° x 71°	830 warm white	3000 K	80
910925866241	BGP761 LED90-/740 II DW10 DGR 62	61° x 150°	740 neutral white	4000 K	70
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	154° - 31° x 54°	740 neutral white	4000 K	70
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	152° - 25° x 66°	740 neutral white	4000 K	70
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	149° - 10° x 57°	740 neutral white	4000 K	70

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	5,952 lm	-	Distribution medium 11
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	5,952 lm	-	Distribution medium 11
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	10,800 lm	-	Distribution narrow 11
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	13,485 lm	-	Distribution medium 70
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	11,830 lm	-	Distribution medium 11
910925866223	BGP762 LED169-/740 I DS50 DGR 62	14,960 lm	-	Distribution symmetrical 50
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	10,010 lm	-	Distribution narrow 10
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	13,500 lm	-	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	15,480 lm	-	Distribution extra wide 10
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	8,918 lm	-	Distribution medium 11
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	12,740 lm	-	Distribution medium 11
910925866229	BGP762 LED170-/830 II DW10 DGR 76	15,300 lm	-	Distribution wide 10
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	8,640 lm	-	Distribution medium 10
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	14,960 lm	-	Distribution symmetrical 50
910925866245	BGP762 LED200-/740 I DW50 DGR 62	17,200 lm	-	Distribution wide 50
910925866246	BGP762 LED210-/740 II DX70 DGR 76	18,060 lm	-	Distribution extra wide 70

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	17,100 lm	-	Distribution wide 10
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	19,800 lm	-	Distribution wide 10
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	10,800 lm	-	Distribution medium 10
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	14,240 lm	-	Distribution medium 10
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	20,700 lm	-	Distribution medium 32
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	18,920 lm	-	Distribution wide 50
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	19,550 lm	-	Distribution extra wide 10
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	13,800 lm	-	Distribution wide 50
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	13,195 lm	-	Distribution medium 32
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	20,700 lm	-	Distribution medium 32
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	900 lm	1	Distribution medium 10
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	1,092 lm	1	Distribution medium 11
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	1,274 lm	1	Distribution narrow 10
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	1,456 lm	1	Distribution narrow 11
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	2,002 lm	1	Distribution medium 50
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	2,136 lm	1	Distribution medium 70
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	2,403 lm	1	Distribution symmetrical 50
910925863563	BGP760 LED30-/830 II DW10 DGR 62	2,730 lm	1	Distribution wide 10
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	2,958 lm	1	Distribution extra wide 10
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	3,784 lm	1	Distribution wide 50
910925863567	BGP760 LED49-/740 II DX70 DGR 62	4,263 lm	1	Distribution extra wide 70
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	2,070 lm	-	Distribution medium 10
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	3,827 lm	-	Distribution medium 10
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	992 lm	-	Distribution medium 11
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	992 lm	-	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	5,340 lm	-	Distribution medium 10
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	4,988 lm	-	Distribution extra wide 10
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	3,480 lm	-	Distribution wide 50
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	4,368 lm	-	Distribution medium 32
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	4,368 lm	-	Distribution medium 32
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	21,360 lm	-	Distribution wide 10
910925866249	BGP763 LED300-/740 I DW50 DGR 62	25,200 lm	-	Distribution wide 50
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	22,100 lm	-	Distribution extra wide 10
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	29,920 lm	-	Distribution wide 10
910925866253	BGP763 LED320-/740 II DX70 DGR 76	26,880 lm	-	Distribution extra wide 70
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	23,140 lm	-	Distribution medium 10
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	31,320 lm	-	Distribution medium 10
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	28,560 lm	-	Distribution medium 50
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	28,560 lm	-	Distribution extra wide 10
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	20,060 lm	-	Distribution wide 50
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	2,790 lm	-	Distribution medium 11
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	2,790 lm	-	Distribution medium 11
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	4,050 lm	-	Distribution medium 10
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	6,660 lm	-	Distribution medium 50
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	8,084 lm	-	Distribution extra wide 10
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	9,790 lm	-	Distribution medium 10
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	5,096 lm	-	Distribution narrow 10
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	7,392 lm	-	Distribution symmetrical 50
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	5,096 lm	-	Distribution medium 11
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	7,476 lm	-	Distribution medium 10

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	4,550 lm	-	Distribution medium 11
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	6,688 lm	-	Distribution medium 70
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	5,400 lm	-	Distribution narrow 11
910925866241	BGP761 LED90-/740 II DW10 DGR 62	8,100 lm	-	Distribution wide 10
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	6,660 lm	-	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	7,476 lm	-	Distribution medium 10
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	10,680 lm	-	Distribution medium 10
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	6,900 lm	-	Distribution wide 50
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	7,462 lm	-	Distribution medium 32

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	69 W
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	55 W
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	81 W
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	106 W
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	72 W
910925866223	BGP762 LED169-/740 I DS50 DGR 62	98 W
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	61 W
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	85 W
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	100 W
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	66 W
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	91 W
910925866229	BGP762 LED170-/830 II DW10 DGR 76	114 W
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	53 W
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	99 W
910925866245	BGP762 LED200-/740 I DW50 DGR 62	114 W
910925866246	BGP762 LED210-/740 II DX70 DGR 76	120 W
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	106 W
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	126 W
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	70 W
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	91 W
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	138 W
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	126 W
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	138 W
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	138 W
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	86 W
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	138 W
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	6.8 W
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	8 W
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	9 W
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	11.8 W
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	13.8 W
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	17 W
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	16 W
910925863563	BGP760 LED30-/830 II DW10 DGR 62	21 W
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	20 W
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	26 W

Order Code	Full Product Name	Power Consumption
910925863567	BGP760 LED49-/740 II DX70 DGR 62	29.5 W
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	15 W
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	26 W
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	13.6 W
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	11.2 W
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	38 W
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	37 W
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	37 W
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	29.5 W
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	33.5 W
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	160 W
910925866249	BGP763 LED300-/740 I DW50 DGR 62	176 W
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	150 W
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	196 W
910925866253	BGP763 LED320-/740 II DX70 DGR 76	182 W
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	154 W
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	215 W
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	196 W
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	198 W
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	198 W
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	34 W
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	27.5 W
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	27 W
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	43.5 W
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	54 W
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	63 W
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	31.5 W
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	49.5 W
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	31.5 W
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	50 W
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	34 W
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	54 W
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	41 W
910925866241	BGP761 LED90-/740 II DW10 DGR 62	51 W
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	43.5 W
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	49.5 W

Order Code	Full Product Name	Power Consumption
910925866497	BGP761 LED119-/740 I DM10 DGR 62 S	72 W
910925867981	BGP761 LED119-/740 I DW50 BL1 DGR CLO IAC	70 W

Order Code	Full Product Name	Power Consumption
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	50 W

**Controls and Dimming**

Order Code	Full Product Name	Dimmable
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	Yes
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	Yes
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Yes
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Yes
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	No
910925866223	BGP762 LED169-/740 I DS50 DGR 62	No
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	No
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	No
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	No
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	Yes
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Yes
910925866229	BGP762 LED170-/830 II DW10 DGR 76	No
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	Yes
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Yes
910925866245	BGP762 LED200-/740 I DW50 DGR 62	No
910925866246	BGP762 LED210-/740 II DX70 DGR 76	No
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	No
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	No
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	Yes
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	No
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Yes
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	Yes
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	Yes
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	Yes
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	Yes
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Yes
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	No
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Yes
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	No
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Yes
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	No
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	Yes
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	No
910925863563	BGP760 LED30-/830 II DW10 DGR 62	No
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	No
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	No
910925863567	BGP760 LED49-/740 II DX70 DGR 62	No
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	Yes

Order Code	Full Product Name	Dimmable
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	Yes
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	Yes
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	Yes
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	Yes
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	Yes
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	Yes
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	Yes
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	Yes
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	No
910925866249	BGP763 LED300-/740 I DW50 DGR 62	No
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	No
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	No
910925866253	BGP763 LED320-/740 II DX70 DGR 76	No
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Yes
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Yes
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	Yes
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	No
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	No
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	Yes
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	Yes
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	No
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	No
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	No
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Yes
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	No
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	No
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	Yes
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	Yes
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Yes
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Yes
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Yes
910925866241	BGP761 LED90-/740 II DW10 DGR 62	No
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Yes
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	No
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Yes
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	Yes
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	Yes

**Mechanical and Housing**

Order Code	Full Product Name	Housing Color
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	Dark gray
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	Dark gray
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Dark gray

Order Code	Full Product Name	Housing Color
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Dark gray
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	Dark gray
910925866223	BGP762 LED169-/740 I DS50 DGR 62	Dark gray

Order Code	Full Product Name	Housing Color
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	Dark gray
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	Dark gray
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	Dark gray
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	Dark gray
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Dark gray
910925866229	BGP762 LED170-/830 II DW10 DGR 76	Dark gray
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	Dark gray
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Dark gray
910925866245	BGP762 LED200-/740 I DW50 DGR 62	Dark gray
910925866246	BGP762 LED210-/740 II DX70 DGR 76	Dark gray
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	Dark gray
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	Dark gray
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	Dark gray
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	Dark gray
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Gray
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	Dark gray
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	Dark gray
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	Dark gray
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	Gray
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Gray
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	Dark gray
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Dark gray
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	Dark gray
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Dark gray
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	Dark gray
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	Dark gray
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	Dark gray
910925863563	BGP760 LED30-/830 II DW10 DGR 62	Dark gray
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	Dark gray
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	Dark gray
910925863567	BGP760 LED49-/740 II DX70 DGR 62	Dark gray
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	Dark gray
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	Dark gray
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	Dark gray
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	Dark gray

Order Code	Full Product Name	Housing Color
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	Dark gray
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	Dark gray
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	Dark gray
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	Gray
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	Dark gray
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	Dark gray
910925866249	BGP763 LED300-/740 I DW50 DGR 62	Dark gray
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	Dark gray
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	Dark gray
910925866253	BGP763 LED320-/740 II DX70 DGR 76	Dark gray
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Dark gray
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Dark gray
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	Dark gray
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	Dark gray
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	Dark gray
910925865604	BGP761 LED45-45/518 II DM11 DGR 62	Dark gray
910925865605	BGP761 LED45-45/420 II DM11 DGR 62	Dark gray
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	Dark gray
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	Dark gray
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	Dark gray
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Dark gray
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	Dark gray
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	Dark gray
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	Dark gray
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	Dark gray
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Dark gray
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Dark gray
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Dark gray
910925866241	BGP761 LED90-/740 II DW10 DGR 62	Dark gray
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Dark gray
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	Dark gray
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Dark gray
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	Dark gray
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	Gray

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865607	BGP762 LED95-45/518 II DM11 DGR 62	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865608	BGP762 LED95-45/420 II DM11 DGR 62	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866223	BGP762 LED169-/740 I DS50 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode



Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866229	BGP762 LED170-/830 II DW10 DGR 76	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866245	BGP762 LED200-/740 I DW50 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866246	BGP762 LED210-/740 II DX70 DGR 76	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925863563	BGP760 LED30-/830 II DW10 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925863567	BGP760 LED49-/740 II DX70 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode



Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866249	BGP763 LED300-/740 I DW50 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866253	BGP763 LED320-/740 II DX70 DGR 76	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866241	BGP761 LED90-/740 II DW10 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866496	BGP761 LED84/740 I DM10 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode			

**Application Conditions**

Order Code	Full Product Name	Maximum dim level
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	Not applicable
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	Not applicable
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Not applicable
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	50%
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	Not applicable
910925866223	BGP762 LED169-/740 I DS50 DGR 62	Not applicable
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	Not applicable
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	Not applicable
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	Not applicable
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	Not applicable
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Not applicable
910925866229	BGP762 LED170-/830 II DW10 DGR 76	Not applicable
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	0% (digital)
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Not applicable
910925866245	BGP762 LED200-/740 I DW50 DGR 62	Not applicable
910925866246	BGP762 LED210-/740 II DX70 DGR 76	Not applicable
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	Not applicable
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	Not applicable
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	Not applicable
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	Not applicable
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	0% (digital)
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	Not applicable
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	0% (digital)
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	0% (digital)
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	50%
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	0% (digital)
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	Not applicable
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Not applicable
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	Not applicable
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Not applicable
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	Not applicable
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	50%
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	Not applicable
910925863563	BGP760 LED30-/830 II DW10 DGR 62	Not applicable
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	Not applicable
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	Not applicable
910925863567	BGP760 LED49-/740 II DX70 DGR 62	Not applicable
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	50%

Order Code	Full Product Name	Maximum dim level
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	50%
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	Not applicable
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	Not applicable
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	Not applicable
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	0% (digital)
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	0% (digital)
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	50%
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	50%
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	Not applicable
910925866249	BGP763 LED300-/740 I DW50 DGR 62	Not applicable
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	Not applicable
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	Not applicable
910925866253	BGP763 LED320-/740 II DX70 DGR 76	Not applicable
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Not applicable
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Not applicable
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	Not applicable
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	0% (digital)
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	0% (digital)
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	Not applicable
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	Not applicable
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	Not applicable
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	Not applicable
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	Not applicable
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	50%
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	Not applicable
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	Not applicable
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	Not applicable
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	50%
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Not applicable
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	50%
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Not applicable
910925866241	BGP761 LED90-/740 II DW10 DGR 62	Not applicable
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Not applicable
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	Not applicable
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Not applicable
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	0% (digital)
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	50%

Polar Wide Diagrams

Polar Normal (separate) - BGP762I -  
910925866229

Polar Normal (separate) - BGP761I -  
910925866232

Polar Normal (separate) - BGP761I -  
910925866242

Polar Normal (separate) - BGP762I -  
910925866225

Polar Normal (separate) - BGP763I -  
910925866249

Polar Normal (separate) - BGP762I -  
910925866228

Polar Normal (separate) - BGP762I -  
910925866243

Polar Normal (separate) - BGP763I -  
910925866251

Polar Normal (separate) - BGP762I -  
910925866220

Polar Wide Diagrams

Polar Normal (separate) - BGP762I -  
910925866221

Polar Normal (separate) - BGP762I -  
910925866246

Polar Normal (separate) - BGP761I -  
910925866497

Polar Normal (separate) - BGP762I -  
910925866492

Polar Normal (separate) - BGP760I -  
910925863562

Polar Normal (separate) - BGP760I -  
910925863561

Polar Normal (separate) - BGP760I -  
910925863564

Polar Normal (separate) - BGP760I -  
910925863554

Polar Normal (separate) - BGP760I -  
910925863567

Polar Wide Diagrams

Polar Normal (separate) - BGP760I -  
910925863563

Polar Normal (separate) - BGP760I -  
910925863566

Polar Normal (separate) - BGP760I -  
910925863560

Polar Normal (separate) - BGP760I -  
910925864083

Polar Normal (separate) - BGP762I -  
910925866223

Polar Normal (separate) - BGP761I -  
910925866230

Polar Normal (separate) - BGP761I -  
910925866238

Polar Normal (separate) - BGP763I -  
910925866250

Polar Normal (separate) - BGP762I -  
910925866227

Polar Wide Diagrams

Polar Normal (separate) - BGP761I -  
910925866233

Polar Normal (separate) - BGP762I -  
910925866224

Polar Normal (separate) - BGP761I -  
910925866235

Polar Normal (separate) - BGP761I -  
910925866236

Polar Normal (separate) - BGP761I -  
910925866241

Polar Normal (separate) - BGP762I -  
910925866222

Polar Normal (separate) - BGP761I -  
910925866234

Polar Normal (separate) - BGP762I -  
910925866247

Polar Normal (separate) - BGP762I -  
910925866252

Polar Wide Diagrams

Polar Normal (separate) - BGP763I -  
910925866248

Polar Normal (separate) - BGP762I -  
910925866226

Polar Normal (separate) - BGP761I -  
910925866237

Polar Normal (separate) - BGP761I -  
910925866239

Polar Normal (separate) - BGP761I -  
910925866240

Polar Normal (separate) - BGP762I -  
910925866245

Polar Normal (separate) - BGP763I -  
910925866253

Polar Normal (separate) - BGP760I -  
910925863556

Polar Normal (separate) - BGP760I -  
910925863557

Polar Wide Diagrams

Polar Normal (separate) - BGP760I -  
910925863555

Polar Normal (separate) - BGP760I -  
910925864084

Polar Normal (separate) - BGP760I -  
910925868855

Polar Normal (separate) - BGP760I -  
910925866307

Polar Normal (separate) - BGP760I -  
910925866306

Polar Normal (separate) - BGP762I -  
910925866493

Polar Normal (separate) - BGP763I -  
910925866494

Polar Normal (separate) - BGP760I -  
910925866495

Polar Normal (separate) - BGP763I -  
910925866498



Polar Wide Diagrams

Polar Normal (separate) - BGP762I -  
910925866963

Polar Normal (separate) - BGP762I -  
910925868786

Polar Normal (separate) - BGP761I -  
910925865605

Polar Normal (separate) - BGP761I -  
910925865604

Polar Normal (separate) - BGP762I -  
910925865607

Polar Normal (separate) - BGP762I -  
910925865608

Polar Normal (separate) - BGP763I -  
910925867852

Polar Normal (separate) - BGP762I -  
910925867851

Polar Normal (separate) - BGP760I -  
910925867978

Polar Wide Diagrams

Polar Normal (separate) - BGP760I -  
910925867979

Polar Normal (separate) - BGP762I -  
910925867982

Polar Normal (separate) - BGP762I -  
910925867983

Polar Normal (separate) - BGP761I -  
910925867981

Polar Normal (separate) - BGP763I -  
910925867985

Polar Normal (separate) - BGP763I -  
910925867984

Polar Normal (separate) - BGP761I -  
910925867988

Polar Normal (separate) - BGP760I -  
910925867995

