



Quiet, reliable operation

Encapsulated Core & Coil (73B)

Where quiet performance is required, the standard open core and coil ballast is encapsulated (potted) in a cube-shaped steel can utilizing Class H (180°C) polyester compound.

Benefits

- Quiet operation
- Includes the benefits of the open core and coil above

Features

- Class A noise rating through 175W and Class B noise rating for 250W and 400W
- Includes the features of the open core and coil above

Application

- Offices, schools, and retail stores


Versions



73B5482500D

Encapsulated Core & Coil (73B)

Dimensional drawing



Product	A1	A2	A3	B1	B2	C1	D1
ENCAPSULATED CORE & COIL HID	6.75 in	6 in	5.4 in	3.8 in	2 in	5 in	0.25 in
MH BAL 250W M58 QUAD ENCAP							

