



Versatility in commercial applications

F-can (72C)

The Philips Advance line of F-can HID ballasts comes in two dual-voltage configurations for the US and Canadian market. Ballasts for these luminaires are most often encased and potted in fluorescent ballast type cans.

Benefits

- Low noise for indoor use
- Two dual voltage configurations available: 120V/277V for the U.S market and 120V/347V for the Canadian market

Features

- Utilizes UL Class A (90°C) insulation
- Has built-in, automatically resetting, thermal protector which disconnects the ballast from power line in the event of overheating

Application

- Offices, schools, and retail stores


F-can (72C)

Versions



72C5582NP

Dimensional drawing



Product	A1	A2	A3	B1	B2	C1	D1
F-CAN HID 72C5281NP900	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C8084NP001	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C7984NP001	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C6082NP001	12 in	18.63 in	18 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C5782NP001	12 in	16.13 in	15.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C5581NP001	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C5381NP001	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C5282NP001	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C5181NP001	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C55C1NP	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C5482NP	12 in	13.75 in	13.13 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C53C1NP	12 in	11.13 in	10.5 in	3.9 in	2.0 in	2.6 in	0.3 in
F-CAN HID 72C5783NP	12 in	16.13 in	15.5 in	3.9 in	2.0 in	2.6 in	0.3 in

Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit
Mechanical and Housing	
Housing	F-Can

Operating and Electrical

Order Code	Full Product Name	Input Voltage
913700501541	F-CAN HID MH BAL 250W M138/153 120/277V FCAN	120/277 V
913700579909	F-CAN HID MH BAL 100W M90/140 120/347V FCAN	120/347 V
913700580109	F-CAN HID MH BAL 150W M102/142 120/277V FCAN	120/277 V
913700580309	F-CAN HID MH BAL 175W M57 120/347V FCAN	120/347 V
913710407301	F-CAN HID MH BAL 50W M110 120/277V FCAN	120/277 V
913710407801	F-CAN HID MH BAL 70W M98/143 120/277V FCAN	120/277 V
913710408101	F-CAN HID MH BAL 100W M90/140 120/277V FCAN	120/277 V

Order Code	Full Product Name	Input Voltage
913710408401	F-CAN HID MH BAL 175W M57 120/277V FCAN	120/277 V
913710408901	F-CAN HID MH BAL 250W M58 120/277V FCAN	120/277 V
913710409201	F-CAN HID MH BAL 400W M59 120/277V FCAN	120/277 V
913710409901	F-CAN HID HPS BAL 70W S62 120/277V FCAN	120/277 V
913710410201	F-CAN HID HPS BAL 100W S54 120/277V FCAN	120/277 V
913710563502	F-CAN HID MH BAL 70W M139 120/277 FCAN	120/277 V

F-can (72C)

General Information

Order Code	Full Product Name	Lamp Type
913700501541	F-CAN HID MH BAL 250W M138/153 120/277V FCAN	250W MH
913700579909	F-CAN HID MH BAL 100W M90/140 120/347V FCAN	100W MH
913700580109	F-CAN HID MH BAL 150W M102/142 120/277V FCAN	150W MH
913700580309	F-CAN HID MH BAL 175W M57 120/347V FCAN	175/150W MH
913710407301	F-CAN HID MH BAL 50W M110 120/277V FCAN	50W MH
913710407801	F-CAN HID MH BAL 70W M98/143 120/277V FCAN	70W MH
913710408101	F-CAN HID MH BAL 100W M90/140 120/277V FCAN	100W MH

Order Code	Full Product Name	Lamp Type
913710408401	F-CAN HID MH BAL 175W M57 120/277V FCAN	175/150W MH
913710408901	F-CAN HID MH BAL 250W M58 120/277V FCAN	250W MH
913710409201	F-CAN HID MH BAL 400W M59 120/277V FCAN	400W MH
913710409901	F-CAN HID HPS BAL 70W S62 120/277V FCAN	70W HPS
913710410201	F-CAN HID HPS BAL 100W S54 120/277V FCAN	100W HPS
913710563502	F-CAN HID MH BAL 70W M139 120/277 FCAN	70W MH

