

Remote mount durability

Indoor Enclosed (78E)

These units are designed for use indoors where the ballast must be mounted remotely from the luminaire. These ballasts are typically used in applications where the luminaire is mounted in an area with very high ambient temperatures. The ballast can be mounted remotely in a cooler location.

Benefits

- Convenient knockouts assist hook-up
- UL Listed for operation remote from the lighting fixture

Features

- Knockouts provided at both ends of the case
- Capacitor and ignitor are contained in a separate compartment
- The case contains the core and coil potted in a Class H (180°C) heat-dissipating resin
- Wall mounting is accomplished by flanges on the top and bottom of the case

Application

- Rugged environments, remote mounting


Indoor Enclosed (78E)

Versions



78E6592WC1

Dimensional drawing



Product	A1	A2	A3	A4	B1	B2	C1	D1
INDOOR ENCLOSED HID	14.4 in	13.4 in	12.7 in	12.1 in	7.7 in	3.3 in	5.8 in	0.4 in
MH BAL 1000W M47 QUAD								
ENCL								
INDOOR ENCLOSED HID	14.4 in	13.4 in	12.7 in	12.1 in	7.7 in	3.3 in	5.8 in	0.4 in
MH BAL 1000W M47 480V								
ENCL								

Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit
Lamp Type	1000W MH
Mechanical and Housing	
Housing	IE

Operating and Electrical

Order Code	Full Product Name	Input Voltage
78E6542001	INDOOR ENCLOSED HID MH BAL 1000W M47 480V	480 V
	ENCL	

Order Code	Full Product Name	Input Voltage
78E6592001	INDOOR ENCLOSED HID MH BAL 1000W M47 QUAD	120/208/240/277 V
	ENCL	

Indoor Enclosed (78E)

