

Remote mount durability

Indoor Enclosed (78E)

These units are designed for use indoors where the ballast must be mounted remotely from the luminaire. These ballasts are typically used in applications where the luminaire is mounted in an area with very high ambient temperatures. The ballast can be mounted remotely in a cooler location.

Avantages

- Convenient knockouts assist hook-up
- UL Listed for operation remote from the lighting fixture

Fonctions

- Knockouts provided at both ends of the case
- Capacitor and ignitor are contained in a separate compartment
- The case contains the core and coil potted in a Class H (180°C) heat-dissipating resin
- Wall mounting is accomplished by flanges on the top and bottom of the case

Application


- Rugged environments, remote mounting

Indoor Enclosed (78E)

Versions



Schéma dimensionnel



Product	A1	A2	A3	A4	B1	B2	C1	D1
INDOOR ENCLOSED HID 78E6592001	14,4 in	13,4 in	12,7 in	12,1 in	7,7 in	3,3 in	5,8 in	0,4 in
INDOOR ENCLOSED HID 78E6542001	14,4 in	13,4 in	12,7 in	12,1 in	7,7 in	3,3 in	5,8 in	0,4 in

Fonctionnement et électricité

Fréquence d'entrée 60 Hz

Renseignements généraux

Nombre de lampes 1 piece/unit

Type de lampe 1000W MH

Mécanique et boîtier

Boîtier IE

Fonctionnement et électricité

Order Code	Full Product Name	Tension d'entrée
194233	INDOOR ENCLOSED HID MH BAL 1000W M47 480V ENCL	480 V

Order Code	Full Product Name	Tension d'entrée
505461	INDOOR ENCLOSED HID MH BAL 1000W M47 QUAD ENCL	120/208/240/277 V

Indoor Enclosed (78E)

