



All-weather performance and reliability

Outdoor Weatherproof (79W)

Outdoor weatherproof ballasts are designed for remote mounting outdoors under all weather conditions. They may also be placed inside a pole base, but care must be taken to avoid areas prone to flood situations as they are not water submersable.

Benefits

- Ballast is suitable for use in most outdoor weather conditions
- UL Listed for operation remote from the lighting fixture

Features

- Integral 1" threaded nipple with locknut facilitates hook-up to electrical conduit or to the mounting bracket when used on a pole

Application

- Billboard, road sign lighting, and some outdoor sports facilities, such as tennis courts


Outdoor Weatherproof (79W)

Versions



79W6586001

Dimensional drawing



Product	B1	B2	B3	C1	C2
OUTDOOR WEATHERPROOF HID 79W6592001	7.3 in	6.4 in	1 in	11.3 in	1.9 in
OUTDOOR WEATHERPROOF HID 79W6351001	7.3 in	6.4 in	1 in	13.8 in	1.9 in
OUTDOOR WEATHERPROOF HID 79W6542001	7.3 in	6.4 in	1 in	11.3 in	1.9 in

Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit
Lamp Type	MH
Mechanical and Housing	
Housing	OW

Operating and Electrical

Order Code	Full Product Name	Input Voltage
913700549509	OUTDOOR WEATHERPROOF HID MH BAL 1000W M47 480V WP	480 V
913700583909	OUTDOOR WEATHERPROOF HID MH BAL 2X400W M59 120/240V WP	120/240 V

Order Code	Full Product Name	Input Voltage
913700584009	OUTDOOR WEATHERPROOF HID MH BAL 1000W M47 QUAD WP	120/208/240/277 V

Outdoor Weatherproof (79W)

