



Sleek design, maximum performance

Postline (74P)

Lantern-type, post-top fixtures mounted on slender poles often require ballasts which fit in the poles. Postline ballasts include a special, elongated core and coil ballast encased and potted in a high temperature resin (Class H, 180°C max.) in cylindrical housings of a diameter to accommodate being placed within a 3" or 4" diameter pole.

Benefits

- Conveniently fits inside a 3" or 4" diameter pole

Features

- Capacitor and ignitor (where required) are included within the can
- Includes leads necessary for direct connection to a photocell
- A 1/2" threaded nipple is provided for verticle mounting
- Leads extend from both ends of the can for ease of installation

Application

- Post top luminaires


Postline (74P)

Versions



74P5104011P

Dimensional drawing



Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit
Mechanical and Housing	
Housing	74P

Operating and Electrical

Order Code	Full Product Name	Input Voltage
74P5104011P	POSTLINE HID MH BAL 50W M110 120V POSTLINE	120 V
74P7703011P	POSTLINE HID HPS BAL 35W S76 120V POSTLINE	120 V
74P7903011P	POSTLINE HID HPS BAL 70W S62 120V POSTLINE	120 V
74P8013011P	POSTLINE HID HPS BAL 100W S54 208V POSTLINE	208 V

General Information

Order Code	Full Product Name	Lamp Type
74P5104011P	POSTLINE HID MH BAL 50W M110 120V POSTLINE	MH
74P7703011P	POSTLINE HID HPS BAL 35W S76 120V POSTLINE	HPS
74P7903011P	POSTLINE HID HPS BAL 70W S62 120V POSTLINE	HPS

Product	B3	C1
POSTLINE HID 74P8104011P	2.55 in	17.6 in
POSTLINE HID 74P8013011P	2.55 in	21 in
POSTLINE HID 74P5104011P	2.55 in	12 in
POSTLINE HID 74P7703011P	2.55 in	7 in
POSTLINE HID 74P7903011P	2.55 in	12 in
POSTLINE HID 74P7803011P	2.55 in	12 in
POSTLINE HID 74P8033011P	2.55 in	21 in

Order Code	Full Product Name	Input Voltage
74P8104011P	POSTLINE HID HPS BAL 150W S55 120V POSTLINE	120 V
74P7803011P	POSTLINE HID HPS BAL 50W S68 120V POSTLINE	120 V
74P8033011P	POSTLINE HID HPS BAL 100W S54 277V POSTLINE	277 V

Order Code	Full Product Name	Lamp Type
74P8013011P	POSTLINE HID HPS BAL 100W S54 208V POSTLINE	HPS
74P8104011P	POSTLINE HID HPS BAL 150W S55 120V POSTLINE	HPS
74P7803011P	POSTLINE HID HPS BAL 50W S68 120V POSTLINE	HPS

Postline (74P)

Order Code	Full Product Name	Lamp Type
74P8033011P	POSTLINE HID HPS BAL 100W S54 277V POSTLINE	HPS

