



Sleek design, maximum performance

Postline (74P)

Lantern-type, post-top fixtures mounted on slender poles often require ballasts which fit in the poles. Postline ballasts include a special, elongated core and coil ballast encased and potted in a high temperature resin (Class H, 180°C max.) in cylindrical housings of a diameter to accommodate being placed within a 3" or 4" diameter pole.

Benefits

- Conveniently fits inside a 3" or 4" diameter pole

Features

- Capacitor and ignitor (where required) are included within the can
- Includes leads necessary for direct connection to a photocell
- A 1/2" threaded nipple is provided for verticle mounting
- Leads extend from both ends of the can for ease of installation

Application

- Post top luminaires


Postline (74P)

Versions



74P5104011P

Dimensional drawing



Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit
Mechanical and Housing	
Housing	74P

Operating and Electrical

Order Code	Full Product Name	Input Voltage
913700506461	POSTLINE HID MH BAL 50W M110 120V POSTLINE	120 V
913700546409	POSTLINE HID HPS BAL 35W S76 120V POSTLINE	120 V
913700546709	POSTLINE HID HPS BAL 70W S62 120V POSTLINE	120 V
913700547209	POSTLINE HID HPS BAL 100W S54 208V POSTLINE	208 V

General Information

Order Code	Full Product Name	Lamp Type
913700506461	POSTLINE HID MH BAL 50W M110 120V POSTLINE	MH
913700546409	POSTLINE HID HPS BAL 35W S76 120V POSTLINE	HPS
913700546709	POSTLINE HID HPS BAL 70W S62 120V POSTLINE	HPS

Product	B3	C1
POSTLINE HID 74P8104011P	2.55 in	17.6 in
POSTLINE HID 74P8013011P	2.55 in	21 in
POSTLINE HID 74P5104011P	2.55 in	12 in
POSTLINE HID 74P7703011P	2.55 in	7 in
POSTLINE HID 74P7903011P	2.55 in	12 in
POSTLINE HID 74P7803011P	2.55 in	12 in
POSTLINE HID 74P8033011P	2.55 in	21 in

Order Code	Full Product Name	Input Voltage
913700547409	POSTLINE HID HPS BAL 150W S55 120V POSTLINE	120 V
913710569301	POSTLINE HID HPS BAL 50W S68 120V POSTLINE	120 V
913710569501	POSTLINE HID HPS BAL 100W S54 277V POSTLINE	277 V

Order Code	Full Product Name	Lamp Type
913700547209	POSTLINE HID HPS BAL 100W S54 208V POSTLINE	HPS
913700547409	POSTLINE HID HPS BAL 150W S55 120V POSTLINE	HPS
913710569301	POSTLINE HID HPS BAL 50W S68 120V POSTLINE	HPS

Postline (74P)

Order Code	Full Product Name	Lamp Type
913710569501	POSTLINE HID HPS BAL 100W S54 277V POSTLINE	HPS

