



Application flexibility

Transformers

Stepdown transformers and autotransformers are used when you need to connect a lower voltage device to a higher voltage source.

优点

- Available in the most common voltages
- Linear transformer design operates cooler than a ballast


特点

- Uses Class H (180°C) insulation
- Convenient J-Box cover w/thermal protector available for some transformers

应用


- High bay retail, manufacturing, gymnasiums, warehouses, parking structures, outdoor

Versions



Transformers

二维绘图



Product	C1	C2	A1	A2	B1	B2
AUTO-TRANSFORMER 71A9843600	3.6 in	2.35 in	2.6 in	2.2 in	2.2 in	1.8 in

