



Application flexibility

Transformers

Stepdown transformers and autotransformers are used when you need to connect a lower voltage device to a higher voltage source.

Benefits

- Available in the most common voltages
- Linear transformer design operates cooler than a ballast

Features

- Uses Class H (180°C) insulation
- Convenient J-Box cover w/thermal protector available for some transformers

Application

- High bay retail, manufacturing, gymnasiums, warehouses, parking structures, outdoor



Versions



71A9741600

Transformers

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
AUTO-TRANSFORMER 71A9843600	3.6 in	2.35 in	2.6 in	2.2 in	2.2 in	1.8 in
AUTO-TRANSFORMER 71A9743600C	2.8 in	1.5 in	2.6 in	2.2 in	2.2 in	1.8 in
AUTO-TRANSFORMER AUTOXFMR 277:115 300VA C&C	3.5 in	2 in	2.6 in	2.2 in	2.2 in	1.8 in

Product	C1	C2	A1	A2	B1	B2
AUTO-TRANSFORMER 71A9862600J	4.7 in	2.7 in	2.63 in	1.81 in	2.19 in	1.84 in
AUTO-TRANSFORMER 71A9839600J	4.2 in	2.2 in	2.63 in	1.81 in	2.19 in	1.84 in
AUTO-TRANSFORMER 71A9741600J	4 in	2 in	2.63 in	1.81 in	2.19 in	1.84 in

Operating and Electrical

Input Frequency 60 Hz

Operating and Electrical

Order Code	Full Product Name	Input Voltage
913700550709	AUTO-TRANSFORMER AUTOXFMR 277:115 300VA C&C	277:120 or 120:277 V
913710559502	AUTO-TRANSFORMER AUTOXFMR 277:115 300VA JBOX	277:120 or 120:277 V
913710559902	AUTO-TRANSFORMER ISOXFMR 120:11.5V 75W C&C	120:12 V

Order Code	Full Product Name	Input Voltage
913710560302	AUTO-TRANSFORMER AUTOXFMR 277:115 200VA JBOX	277:120 V
913710560602	AUTO-TRANSFORMER AUTOXFMR 347:120/277 395VA JBOX	347:(120/277) V
913710663402	AUTO-TRANSFORMER AUTOXFMR 480:277 350VA C&C	347:190 or 480:270 V

Mechanical and Housing

Order Code	Full Product Name	Housing
913700550709	AUTO-TRANSFORMER AUTOXFMR 277:115 300VA C&C	NA
913710559502	AUTO-TRANSFORMER AUTOXFMR 277:115 300VA JBOX	Coil cover with 1-2 NIP
913710559902	AUTO-TRANSFORMER ISOXFMR 120:11.5V 75W C&C	NA

Order Code	Full Product Name	Housing
913710560302	AUTO-TRANSFORMER AUTOXFMR 277:115 200VA JBOX	Coil cover with 1-2 NIP
913710560602	AUTO-TRANSFORMER AUTOXFMR 347:120/277 395VA JBOX	Coil cover with 1-2 NIP
913710663402	AUTO-TRANSFORMER AUTOXFMR 480:277 350VA C&C	NA

