



# Everything you need in one kit

## Val-U-Pak Plus (77L)

Our VAL-U-PAK Plus magnetic HID replacement kits assemble the required components — including lamp, core and coil, the appropriate capacitor, ignitor (where required), mounting bracket and hardware, and instructions — in one convenient package. This saves valuable time for MRO and contractor applications.

### Benefits

- Vacuum-pressure impregnation is used to re-enforce the electrical insulation of the ballast, preclude moisture, inhibit noise, and dissipate heat
- Pre-insulated voltage leads reduce the risk of shock and shrink installation time

### Features


- Vacuum-pressure impregnated with a silica-filled polyester varnish
- Added versatility, 5-Tap core and coil ballasts for the six most popular applications
- Premium Philips grade clear lamp supplied in kit
- Pre-insulated voltage leads
- Ballast kits supplied with pre-wired ignitor

### Application

- High bay retail, manufacturing, gymnasiums, warehouses, parking structures, outdoor

# Val-U-Pak Plus (77L)



## Versions



77L6552001

77L5570001D

## Dimensional drawing



Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit

## Operating and Electrical

Order Code	Full Product Name	Input Voltage
77L6552001	CORE & COIL HID MH BAL 1000W M47 5-TAP KIT WITH LAMP	120/208/240/277/480 V

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 1000W M47 5-TAP KIT WITH LAMP	5.60 in	3.90 in	4.8 in	4.4 in	4.3 in	3.9 in

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP	4.45 in	2.34 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID MH BAL 250W M58 5-TAP KIT WITH LAMP	3.1 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in

Order Code	Full Product Name	Input Voltage
77L5570001D	CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP	120/208/240/277 V

## Val-U-Pak Plus (77L)

Order Code	Full Product Name	Input Voltage
77L5750001D	CORE & COIL HID MH BAL 250W M58 5-TAP KIT WITH LAMP	120/208/240/277/480 V

Order Code	Full Product Name	Input Voltage
77L6051001D	CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP	120/208/240/277/480 V

### General Information

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
77L6552001	CORE & COIL HID MH BAL 1000W M47 5-TAP KIT WITH LAMP	24 MFD	1000W MH
77L5570001D	CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP	10 MFD	175/150W MH

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
77L5750001D	CORE & COIL HID MH BAL 250W M58 5-TAP KIT WITH LAMP	15 MFD	250W MH
77L6051001D	CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP	24 MFD	400W MH

