



Everything you need in one kit

Val-U-Pak Plus (77L)

Our VAL-U-PAK Plus magnetic HID replacement kits assemble the required components — including lamp, core and coil, the appropriate capacitor, ignitor (where required), mounting bracket and hardware, and instructions — in one convenient package. This saves valuable time for MRO and contractor applications.

Benefits

- Vacuum-pressure impregnation is used to re-enforce the electrical insulation of the ballast, preclude moisture, inhibit noise, and dissipate heat
- Pre-insulated voltage leads reduce the risk of shock and shrink installation time

Features


- Vacuum-pressure impregnated with a silica-filled polyester varnish
- Added versatility, 5-Tap core and coil ballasts for the six most popular applications
- Premium Philips grade clear lamp supplied in kit
- Pre-insulated voltage leads
- Ballast kits supplied with pre-wired ignitor

Application

- High bay retail, manufacturing, gymnasiums, warehouses, parking structures, outdoor

Val-U-Pak Plus (77L)



Versions



77L6552001

77L5570001D

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 77L6051001D	4.45 in	2.34 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 77L5750001D	3.1 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 77L5570001D	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 77L6552001	5.60 in	3.90 in	4.8 in	4.4 in	4.3 in	3.9 in

Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit

Operating and Electrical

Order Code	Full Product Name	Input Voltage
913710411001	CORE & COIL HID MH BAL 1000W M47 5-TAP KIT WITH LAMP	120/208/240/277/480 V

Order Code	Full Product Name	Input Voltage
913710416101	CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP	120/208/240/277 V

Val-U-Pak Plus (77L)

Order Code	Full Product Name	Input Voltage
913710416201	CORE & COIL HID MH BAL 250W M58 5-TAP KIT WITH LAMP	120/208/240/277/480 V

Order Code	Full Product Name	Input Voltage
913710416301	CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP	120/208/240/277/480 V

General Information

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
913710411001	CORE & COIL HID MH BAL 1000W M47 5-TAP KIT WITH LAMP	24 MFD	1000W MH
913710416101	CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP	10 MFD	175/150W MH

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
913710416201	CORE & COIL HID MH BAL 250W M58 5-TAP KIT WITH LAMP	15 MFD	250W MH
913710416301	CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP	24 MFD	400W MH

