



CoreLine Wall-mounted – the clear choice for LED

CoreLine Wall-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Up to 55% energy savings compared with luminaires with PL-C lamps
- Direct replacement for traditional wall-mounted luminaires
- Complete range covering all application requirements in one product (light levels, IP65, IK10, certified emergency lighting, built-in controls)

Features

- Unobtrusive design
- Three lumen packages replacing traditional wall-mounted luminaires with 1x18 W / 2x18 W / 2x26 W PL-C
- Water- and vandal-proof as standard
- Phase-cut dimming as standard
- Frosted diffuser ensuring homogeneous light effect and visual comfort
- Optional emergency lighting
- Optional on/off movement detection or programmed 100%-10%-0% corridor dimming functionality

CoreLine Wall-mounted

Application

- Corridors
- Staircases
- Public entrance areas
- Bathrooms
- Emergency exits
- Parking garages
- Outdoor safety lighting

Specifications

Type	WL130V (slim version)
	WL131V (deeper version)
Light source	Non-replaceable LED module
Power (+/-10%)	12 W (LED12S version)
	22 W (LED20S version)
	36 W (LED34S version)
Beam angle	120°
Luminous flux	1200 lm (LED12S version)
	2000 lm (LED20S version)
	3400 lm (LED34S version)
Correlated Color Temperature	3000 or 4000 K
Color Rendering Index	≥ 80
Median useful life	50,000 hours
L70B50	
Median useful life	38,000 hours
L80B50	
Median useful life	18,000 hours
L90B50	
Average ambient temperature	+25 °C

Operating temperature range	-20 to +35 °C (wall-mounted position)
	-20 to +25 °C (ceiling-mounted position)
	0 to +25 °C (emergency lighting)
Driver	Built-in, replaceable
Mains voltage	220-240V / 50-60 Hz
Dimming	Non-dimmable (PSU versions)
	Dimmable (PSR and DALI versions)
Options	Emergency lighting (integrated): 3 hours (EL3)
	Movement detection unit (integrated): on/off switch with day light override including grouping functionality (MDU)
	DALI driver and movement detection unit (integrated)
Material	Housing: Polyamide
	Difuser: high grade polycarbonate, UV resistant
Color	White (RAL 9003)
Optical cover	Polycarbonate difuser
Connection	Push-in connector
Maintenance	LED module closed, no internal cleaning required
Installation	Screw mounting, directly onto surface
	4-point screw installation of housing to wall
	Twist lock connection diffuser to housing
	Through-wiring possible

Versions



CoreLine Wall-mounted




CoreLine Wall-Mounted Gen2

CoreLine Wall-mounted

Product details



CoreLine_Wall-mounted-
WL131V_D35_CTO_PSD-DPP.TIF




CoreLine_Wall-mounted-
WL130V-2DPP.TIF



CoreLine_Wall-mounted-
WL131V_D35_CTO_PSR_MDU-
DPP.TIF



CoreLine_Wall-mounted-
WL130V_CTO-DPP.TIF



CoreLine_Wall-mounted-
WL130V-1DPP.TIF



CoreLine_Wall-mounted-
WL130V_D35_CTO_MDU-DPP.TIF

CoreLine Wall-mounted

Application Conditions

Ambient temperature range -20 to +40 °C

Approval and Application

Mech. impact protection code IK08

Ingress protection code IP65

Operating and Electrical

Input Voltage 220-240 V

General Information

Beam angle of light source 120 °

CE mark CE mark

Driver included Yes

ENEC mark ENEC mark

Number of gear units 1 unit

Optic type Opal prismatic reflector

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Mechanical and Housing

Color White

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
40268600	WL131V LED12S/830 PSED EL3 WH	10%	No
40269300	WL131V LED12S/840 PSED EL3 WH	10%	No
40270900	WL131V LED20S/830 PSED EL3 WH	10%	No
40271600	WL131V LED20S/840 PSED EL3 WH	10%	No
40272300	WL131V LED34S/830 PSED WH	10%	No
40273000	WL131V LED34S/840 PSED WH	10%	No
40274700	WL131V LED34S/830 PSED EL3 WH	10%	No
40275400	WL131V LED34S/840 PSED EL3 WH	10%	No
40282200	WL131V LED12S/830 PSR EL3 MDU WH	20%	Yes
40283900	WL131V LED12S/840 PSR EL3 MDU WH	20%	Yes
40284600	WL131V LED20S/830 PSR EL3 MDU WH	20%	Yes
40285300	WL131V LED20S/840 PSR EL3 MDU WH	20%	Yes
40286000	WL131V LED34S/830 PSR EL3 MDU WH	20%	Yes
40287700	WL131V LED34S/840 PSR EL3 MDU WH	20%	Yes
38784699	WL131V LED34S/830 PSU WH	Not applicable	Yes
38785399	WL131V LED34S/840 PSU WH	Not applicable	Yes
38786099	WL131V LED12S/830 PSR MDU WH	10%	Yes
38787799	WL131V LED12S/840 PSR MDU WH	10%	Yes
38788499	WL131V LED20S/830 PSR MDU WH	10%	Yes
38789199	WL131V LED20S/840 PSR MDU WH	10%	Yes
38790799	WL131V LED34S/830 PSR MDU WH	10%	Yes
38791499	WL131V LED34S/840 PSR MDU WH	10%	Yes
38792199	WL131V LED12S/830 PSED WH	10%	Yes
38793899	WL131V LED12S/840 PSED WH	10%	Yes
38794599	WL131V LED20S/830 PSED WH	10%	Yes
38795299	WL131V LED20S/840 PSED WH	10%	Yes
38778599	WL130V LED12S/830 PSU WH	Not applicable	Yes
38779299	WL130V LED12S/840 PSU WH	Not applicable	Yes
38780899	WL130V LED20S/830 PSU WH	Not applicable	Yes
38781599	WL130V LED20S/840 PSU WH	Not applicable	Yes
38782299	WL130V LED20S/830 PSU MDU WH	Not applicable	Yes
38783999	WL130V LED20S/840 PSU MDU WH	Not applicable	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
40268600	WL131V LED12S/830 PSED EL3 WH	Yes	38784699	WL131V LED34S/830 PSU WH	No
40269300	WL131V LED12S/840 PSED EL3 WH	Yes	38785399	WL131V LED34S/840 PSU WH	No
40270900	WL131V LED20S/830 PSED EL3 WH	Yes	38786099	WL131V LED12S/830 PSR MDU WH	Yes
40271600	WL131V LED20S/840 PSED EL3 WH	Yes	38787799	WL131V LED12S/840 PSR MDU WH	Yes
40272300	WL131V LED34S/830 PSED WH	Yes	38788499	WL131V LED20S/830 PSR MDU WH	Yes
40273000	WL131V LED34S/840 PSED WH	Yes	38789199	WL131V LED20S/840 PSR MDU WH	Yes
40274700	WL131V LED34S/830 PSED EL3 WH	Yes	38790799	WL131V LED34S/830 PSR MDU WH	Yes
40275400	WL131V LED34S/840 PSED EL3 WH	Yes	38791499	WL131V LED34S/840 PSR MDU WH	Yes
40282200	WL131V LED12S/830 PSR EL3 MDU WH	Yes	38792199	WL131V LED12S/830 PSED WH	Yes
40283900	WL131V LED12S/840 PSR EL3 MDU WH	Yes	38793899	WL131V LED12S/840 PSED WH	Yes
40284600	WL131V LED20S/830 PSR EL3 MDU WH	Yes	38794599	WL131V LED20S/830 PSED WH	Yes
40285300	WL131V LED20S/840 PSR EL3 MDU WH	Yes	38795299	WL131V LED20S/840 PSED WH	Yes
40286000	WL131V LED34S/830 PSR EL3 MDU WH	Yes	38778599	WL130V LED12S/830 PSU WH	No
40287700	WL131V LED34S/840 PSR EL3 MDU WH	Yes	38779299	WL130V LED12S/840 PSU WH	No

CoreLine Wall-mounted

Order Code	Full Product Name	Dimmable
38780899	WL130V LED20S/830 PSU WH	No
38781599	WL130V LED20S/840 PSU WH	No

Order Code	Full Product Name	Dimmable
38782299	WL130V LED20S/830 PSU MDU WH	No
38783999	WL130V LED20S/840 PSU MDU WH	No

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Protection class IEC	Optical cover/ lens type	Emergency lighting
40268600	WL131V LED12S/830 PSED EL3 WH	-	Safety class II (II)	-	No
40269300	WL131V LED12S/840 PSED EL3 WH	-	Safety class II (II)	-	No
40270900	WL131V LED20S/830 PSED EL3 WH	-	Safety class II (II)	-	No
40271600	WL131V LED20S/840 PSED EL3 WH	-	Safety class II (II)	-	EL3
40272300	WL131V LED34S/830 PSED WH	-	Safety class II (II)	-	No
40273000	WL131V LED34S/840 PSED WH	-	Safety class II (II)	-	No
40274700	WL131V LED34S/830 PSED EL3 WH	-	Safety class II (II)	-	No
40275400	WL131V LED34S/840 PSED EL3 WH	-	Safety class II (II)	-	No
40282200	WL131V LED12S/830 PSR EL3 MDU WH	-	Safety class I (I)	-	No
40283900	WL131V LED12S/840 PSR EL3 MDU WH	-	Safety class I (I)	-	No
40284600	WL131V LED20S/830 PSR EL3 MDU WH	-	Safety class I (I)	-	No
40285300	WL131V LED20S/840 PSR EL3 MDU WH	-	Safety class I (I)	-	No
40286000	WL131V LED34S/830 PSR EL3 MDU WH	-	Safety class I (I)	-	No
40287700	WL131V LED34S/840 PSR EL3 MDU WH	-	Safety class I (I)	-	No
38784699	WL131V LED34S/830 PSU WH	-	Safety class II (II)	OP	-
38785399	WL131V LED34S/840 PSU WH	-	Safety class II (II)	OP	-

Order Code	Full Product Name	Cap-Base	Protection class IEC	Optical cover/ lens type	Emergency lighting
38786099	WL131V LED12S/830 PSR MDU WH	-	Safety class I (I)	OP	-
38787799	WL131V LED12S/840 PSR MDU WH	-	Safety class I (I)	OP	-
38788499	WL131V LED20S/830 PSR MDU WH	-	Safety class I (I)	OP	-
38789199	WL131V LED20S/840 PSR MDU WH	-	Safety class I (I)	OP	-
38790799	WL131V LED34S/830 PSR MDU WH	-	Safety class I (I)	OP	-
38791499	WL131V LED34S/840 PSR MDU WH	-	Safety class I (I)	OP	-
38792199	WL131V LED12S/830 PSED WH	-	Safety class II (II)	OP	-
38793899	WL131V LED12S/840 PSED WH	-	Safety class II (II)	OP	-
38794599	WL131V LED20S/830 PSED WH	-	Safety class II (II)	OP	-
38795299	WL131V LED20S/840 PSED WH	-	Safety class II (II)	OP	-
38778599	WL130V LED12S/830 PSU WH	-	Safety class II (II)	OP	-
38779299	WL130V LED12S/840 PSU WH	-	Safety class II (II)	OP	-
38780899	WL130V LED20S/830 PSU WH	-	Safety class II (II)	OP	-
38781599	WL130V LED20S/840 PSU WH	-	Safety class II (II)	OP	-
38782299	WL130V LED20S/830 PSU MDU WH	-	Safety class II (II)	OP	-
38783999	WL130V LED20S/840 PSU MDU WH	-	Safety class II (II)	OP	-

CoreLine Wall-mounted

General Information (2/2)

Order Code	Full Product Name	Flammability mark	Gear	Glow-wire test	Lamp family code	Embedded control	Light source replaceable	Product Family Code
40268600	WL131V LED12S/830 PSED EL3 WH	F	-	650/30	LED12	No	Yes	WL131V
40269300	WL131V LED12S/840 PSED EL3 WH	F	-	650/30	LED12	No	Yes	WL131V
40270900	WL131V LED20S/830 PSED EL3 WH	F	-	650/30	LED20	No	Yes	WL131V
40271600	WL131V LED20S/840 PSED EL3 WH	F	-	650/30	LED20	No	Yes	WL131V
40272300	WL131V LED34S/830 PSED WH	F	-	650/30	LED34S	No	Yes	WL131V
40273000	WL131V LED34S/840 PSED WH	F	-	650/30	LED34S	No	Yes	WL131V
40274700	WL131V LED34S/830 PSED EL3 WH	F	-	650/30	LED34S	No	Yes	WL131V
40275400	WL131V LED34S/840 PSED EL3 WH	F	-	650/30	LED34S	No	Yes	WL131V
40282200	WL131V LED12S/830 PSR EL3 MDU WH	F	-	650/30	LED12	No	Yes	WL131V
40283900	WL131V LED12S/840 PSR EL3 MDU WH	F	-	650/30	LED12	No	Yes	WL131V
40284600	WL131V LED20S/830 PSR EL3 MDU WH	F	-	650/30	LED20	No	Yes	WL131V
40285300	WL131V LED20S/840 PSR EL3 MDU WH	F	-	650/30	LED20	No	Yes	WL131V
40286000	WL131V LED34S/830 PSR EL3 MDU WH	F	-	650/30	LED34S	No	Yes	WL131V
40287700	WL131V LED34S/840 PSR EL3 MDU WH	F	-	650/30	LED34S	No	Yes	WL131V
38784699	WL131V LED34S/830 PSU WH	NO	-	650/5	-	-	No	-
38785399	WL131V LED34S/840 PSU WH	NO	-	650/5	-	-	No	-
38786099	WL131V LED12S/830 PSR MDU WH	NO	-	650/5	-	-	No	-
38787799	WL131V LED12S/840 PSR MDU WH	NO	-	650/5	-	-	No	-
38788499	WL131V LED20S/830 PSR MDU WH	NO	-	650/5	-	-	No	-
38789199	WL131V LED20S/840 PSR MDU WH	NO	-	650/5	-	-	No	-
38790799	WL131V LED34S/830 PSR MDU WH	NO	-	650/5	-	-	No	-
38791499	WL131V LED34S/840 PSR MDU WH	NO	-	650/5	-	-	No	-
38792199	WL131V LED12S/830 PSED WH	NO	-	650/5	-	-	No	-
38793899	WL131V LED12S/840 PSED WH	NO	-	650/5	-	-	No	-
38794599	WL131V LED20S/830 PSED WH	NO	-	650/5	-	-	No	-
38795299	WL131V LED20S/840 PSED WH	NO	-	650/5	-	-	No	-
38778599	WL130V LED12S/830 PSU WH	NO	-	650/5	-	-	No	-
38779299	WL130V LED12S/840 PSU WH	NO	-	650/5	-	-	No	-
38780899	WL130V LED20S/830 PSU WH	NO	-	650/5	-	-	No	-
38781599	WL130V LED20S/840 PSU WH	NO	-	650/5	-	-	No	-
38782299	WL130V LED20S/830 PSU MDU WH	NO	-	650/5	-	-	No	-
38783999	WL130V LED20S/840 PSU MDU WH	NO	-	650/5	-	-	No	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
40268600	WL131V LED12S/830 PSED EL3 WH	(0.4388,0.4081)	3000 K	89	100 lm/W
40269300	WL131V LED12S/840 PSED EL3 WH	(0.3822,0.3817)	4000 K	89	100 lm/W
40270900	WL131V LED20S/830 PSED WH	(0.4388,0.4081)	3000 K	89	91 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
40271600	WL131V LED20S/840 PSED EL3 WH	(0.3822,0.3817)	4000 K	89	91 lm/W
40272300	WL131V LED34S/830 PSED WH	(0.4388,0.4081)	3000 K	89	94 lm/W

CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
40273000	WL131V LED34S/840 PSED WH	(0.3822,0.3817)	4000 K	89	94 lm/W
40274700	WL131V LED34S/830 PSED EL3 WH	(0.4388,0.4081)	3000 K	89	94 lm/W
40275400	WL131V LED34S/840 PSED EL3 WH	(0.3822,0.3817)	4000 K	89	94 lm/W
40282200	WL131V LED12S/830 PSR EL3 MDU WH	(0.4388,0.4081)	3000 K	89	100 lm/W
40283900	WL131V LED12S/840 PSR EL3 MDU WH	(0.3822,0.3817)	4000 K	89	100 lm/W
40284600	WL131V LED20S/830 PSR EL3 MDU WH	(0.4388,0.4081)	3000 K	89	91 lm/W
40285300	WL131V LED20S/840 PSR EL3 MDU WH	(0.3822,0.3817)	4000 K	89	91 lm/W
40286000	WL131V LED34S/830 PSR EL3 MDU WH	(0.4388,0.4081)	3000 K	89	94 lm/W
40287700	WL131V LED34S/840 PSR EL3 MDU WH	(0.3822,0.3817)	4000 K	89	94 lm/W
38784699	WL131V LED34S/830 PSU WH	(0.4440, 0.4111)	3000 K	80	95 lm/W
38785399	WL131V LED34S/840 PSU WH	(0.3883, 0.3876)	4000 K	80	95 lm/W
38786099	WL131V LED12S/830 PSR MDU WH	(0.4440, 0.4111)	3000 K	80	80 lm/W
38787799	WL131V LED12S/840	(0.3883, 0.3876)	4000 K	80	80 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PSR MDU WH				
38788499	WL131V LED20S/830 PSR MDU WH	(0.4440, 0.4111)	3000 K	80	80 lm/W
38789199	WL131V LED20S/840 PSR MDU WH	(0.3883, 0.3876)	4000 K	80	80 lm/W
38790799	WL131V LED34S/830 PSR MDU WH	(0.4440, 0.4111)	3000 K	80	90 lm/W
38791499	WL131V LED34S/840 PSR MDU WH	(0.3883, 0.3876)	4000 K	80	90 lm/W
38792199	WL131V LED12S/830 PSED WH	(0.4440, 0.4111)	3000 K	80	90 lm/W
38793899	WL131V LED12S/840 PSED WH	(0.3883, 0.3876)	4000 K	80	90 lm/W
38794599	WL131V LED20S/830 PSED WH	(0.4440, 0.4111)	3000 K	80	90 lm/W
38795299	WL131V LED20S/840 PSED WH	(0.3883, 0.3876)	4000 K	80	90 lm/W
38778599	WL130V LED12S/830 PSU WH	(0.4440, 0.4111)	3000 K	80	100 lm/W
38779299	WL130V LED12S/840 PSU WH	(0.3883, 0.3876)	4000 K	80	100 lm/W
38780899	WL130V LED20S/830 PSU WH	(0.4440, 0.4111)	3000 K	80	90 lm/W
38781599	WL130V LED20S/840 PSU WH	(0.3883, 0.3876)	4000 K	80	90 lm/W
38782299	WL130V LED20S/830 PSU MDU WH	(0.4440, 0.4111)	3000 K	80	80 lm/W
38783999	WL130V LED20S/840 PSU MDU WH	(0.3883, 0.3876)	4000 K	80	80 lm/W

CoreLine Wall-mounted

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
40268600	WL131V LED12S/830 PSED EL3 WH	1200 lm	12 W
40269300	WL131V LED12S/840 PSED EL3 WH	1200 lm	12 W
40270900	WL131V LED20S/830 PSED EL3 WH	2000 lm	22 W
40271600	WL131V LED20S/840 PSED EL3 WH	2000 lm	22 W
40272300	WL131V LED34S/830 PSED WH	3400 lm	36 W
40273000	WL131V LED34S/840 PSED WH	3400 lm	36 W
40274700	WL131V LED34S/830 PSED EL3 WH	3400 lm	36 W
40275400	WL131V LED34S/840 PSED EL3 WH	3400 lm	36 W
40282200	WL131V LED12S/830 PSR EL3 MDU WH	1200 lm	12 W
40283900	WL131V LED12S/840 PSR EL3 MDU WH	1200 lm	12 W
40284600	WL131V LED20S/830 PSR EL3 MDU WH	2000 lm	22 W
40285300	WL131V LED20S/840 PSR EL3 MDU WH	2000 lm	22 W
40286000	WL131V LED34S/830 PSR EL3 MDU WH	3400 lm	36 W
40287700	WL131V LED34S/840 PSR EL3 MDU WH	3400 lm	36 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
38784699	WL131V LED34S/830 PSU WH	3400 lm	36 W
38785399	WL131V LED34S/840 PSU WH	3400 lm	36 W
38786099	WL131V LED12S/830 PSR MDU WH	1200 lm	15 W
38787799	WL131V LED12S/840 PSR MDU WH	1200 lm	15 W
38788499	WL131V LED20S/830 PSR MDU WH	2000 lm	25 W
38789199	WL131V LED20S/840 PSR MDU WH	2000 lm	25 W
38790799	WL131V LED34S/830 PSR MDU WH	3400 lm	38 W
38791499	WL131V LED34S/840 PSR MDU WH	3400 lm	38 W
38792199	WL131V LED12S/830 PSED WH	1200 lm	13 W
38793899	WL131V LED12S/840 PSED WH	1200 lm	13 W
38794599	WL131V LED20S/830 PSED WH	2000 lm	23 W
38795299	WL131V LED20S/840 PSED WH	2000 lm	23 W
38778599	WL130V LED12S/830 PSU WH	1200 lm	12 W
38779299	WL130V LED12S/840 PSU WH	1200 lm	12 W
38780899	WL130V LED20S/830 PSU WH	2000 lm	22 W
38781599	WL130V LED20S/840 PSU WH	2000 lm	22 W
38782299	WL130V LED20S/830 PSU MDU WH	2000 lm	23 W
38783999	WL130V LED20S/840 PSU MDU WH	2000 lm	23 W

Mechanical and Housing

Order Code	Full Product Name	Diameter	Width
40268600	WL131V LED12S/830 PSED EL3 WH	-	- mm
40269300	WL131V LED12S/840 PSED EL3 WH	-	- mm
40270900	WL131V LED20S/830 PSED EL3 WH	-	- mm
40271600	WL131V LED20S/840 PSED EL3 WH	-	- mm
40272300	WL131V LED34S/830 PSED WH	-	- mm
40273000	WL131V LED34S/840 PSED WH	-	- mm
40274700	WL131V LED34S/830 PSED EL3 WH	-	- mm
40275400	WL131V LED34S/840 PSED EL3 WH	-	- mm
40282200	WL131V LED12S/830 PSR EL3 MDU WH	-	- mm
40283900	WL131V LED12S/840 PSR EL3 MDU WH	-	- mm
40284600	WL131V LED20S/830 PSR EL3 MDU WH	-	- mm
40285300	WL131V LED20S/840 PSR EL3 MDU WH	-	- mm
40286000	WL131V LED34S/830 PSR EL3 MDU WH	-	- mm
40287700	WL131V LED34S/840 PSR EL3 MDU WH	-	- mm
38784699	WL131V LED34S/830 PSU WH	-	-
38785399	WL131V LED34S/840 PSU WH	-	-

Order Code	Full Product Name	Diameter	Width
38786099	WL131V LED12S/830 PSR MDU WH	-	-
38787799	WL131V LED12S/840 PSR MDU WH	-	-
38788499	WL131V LED20S/830 PSR MDU WH	-	-
38789199	WL131V LED20S/840 PSR MDU WH	-	-
38790799	WL131V LED34S/830 PSR MDU WH	-	-
38791499	WL131V LED34S/840 PSR MDU WH	-	-
38792199	WL131V LED12S/830 PSED WH	-	-
38793899	WL131V LED12S/840 PSED WH	-	-
38794599	WL131V LED20S/830 PSED WH	-	-
38795299	WL131V LED20S/840 PSED WH	-	-
38778599	WL130V LED12S/830 PSU WH	-	-
38779299	WL130V LED12S/840 PSU WH	-	-
38780899	WL130V LED20S/830 PSU WH	-	-
38781599	WL130V LED20S/840 PSU WH	-	-
38782299	WL130V LED20S/830 PSU MDU WH	-	-
38783999	WL130V LED20S/840 PSU MDU WH	-	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
40268600	WL131V LED12S/830 PSED EL3 WH	38000 h	18000 h
40269300	WL131V LED12S/840 PSED EL3 WH	38000 h	18000 h
40270900	WL131V LED20S/830 PSED EL3 WH	38000 h	18000 h
40271600	WL131V LED20S/840 PSED EL3 WH	38000 h	18000 h

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
40272300	WL131V LED34S/830 PSED WH	38000 h	18000 h
40273000	WL131V LED34S/840 PSED WH	38000 h	18000 h
40274700	WL131V LED34S/830 PSED EL3 WH	38000 h	18000 h
40275400	WL131V LED34S/840 PSED EL3 WH	38000 h	18000 h

CoreLine Wall-mounted

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
40282200	WL131V LED12S/830 PSR EL3 MDU WH	38000 h	18000 h
40283900	WL131V LED12S/840 PSR EL3 MDU WH	38000 h	18000 h
40284600	WL131V LED20S/830 PSR EL3 MDU WH	38000 h	18000 h
40285300	WL131V LED20S/840 PSR EL3 MDU WH	38000 h	18000 h
40286000	WL131V LED34S/830 PSR EL3 MDU WH	38000 h	18000 h
40287700	WL131V LED34S/840 PSR EL3 MDU WH	38000 h	18000 h
38784699	WL131V LED34S/830 PSU WH	38000 h	18000 h
38785399	WL131V LED34S/840 PSU WH	38000 h	18000 h
38786099	WL131V LED12S/830 PSR MDU WH	38000 h	18000 h

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
38787799	WL131V LED12S/840 PSR MDU WH	38000 h	18000 h
38788499	WL131V LED20S/830 PSR MDU WH	38000 h	18000 h
38789199	WL131V LED20S/840 PSR MDU WH	38000 h	18000 h
38790799	WL131V LED34S/830 PSR MDU WH	38000 h	18000 h
38791499	WL131V LED34S/840 PSR MDU WH	38000 h	18000 h
38792199	WL131V LED12S/830 PSED WH	38000 h	18000 h
38793899	WL131V LED12S/840 PSED WH	38000 h	18000 h
38794599	WL131V LED20S/830 PSED WH	38000 h	18000 h
38795299	WL131V LED20S/840 PSED WH	38000 h	18000 h
38778599	WL130V LED12S/830 PSU WH	-	-
38779299	WL130V LED12S/840 PSU WH	-	-
38780899	WL130V LED20S/830 PSU WH	-	-
38781599	WL130V LED20S/840 PSU WH	-	-
38782299	WL130V LED20S/830 PSU MDU WH	-	-
38783999	WL130V LED20S/840 PSU MDU WH	-	-

