



CoreLine waterproof – For every project where light really matters

CoreLine Waterproof

CoreLine waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. CoreLine waterproof products can directly replace traditional waterproof luminaires with fluorescent lamps ranging from 18W up to 58W. With its slim and stylish design, it continues to keep its well-known and appreciated architecture. Installation is quick and easy, all thanks to its efficient design. CoreLine waterproof provides better wide-beam light distribution for straightforward and effective lighting. Interact Ready luminaires with integrated wireless communications are also available in this range, ready to be used with Interact gateways, sensors and software.

Benefits

- Energy savings and longer lifetime to reduce operating costs
- Robust design enabling smarter, simpler and faster installation
- Uniform, wide-beam light distribution, which supports easy and attractive lighting design

CoreLine Waterproof

Features

- Energy efficient and long lifetime: up to 140lm/W and 50khrs L75 lifetime
- Many options available: L600/1200/1500, up to 8000lm, 4000K
- Smart product architecture with electrical and mechanical design supporting ease and flexibility of installation (longer sliders, faster lock opening, toolless electrical connections)
- Optional controls and versions available: DALI, Integrated wireless connectivity (Interact Ready), Sensors (MDU), Emergency Lighting (EL), waterproof external connector for easier installation (WEC), through wiring (TW)

Application

- Parking Garages
- Manufacturing
- Warehouses
- General lighting

Specifications

Type	WT120C
Light source	LED module
Power	17.6 W (LED18S L600 version)
	23.5 W (LED22S L1200 version)
	32 W (LED40S L1200 version)
	29.5 W (LED34S L1500 version)
	48 W (LED60S L1500 version)
Beam angle	60°
Luminous flux	2100 lm (LED18S L600 version)
	2900 lm (LED22S L1200 version)
	4100 lm (LED40S L1200 version)
	3500 lm (LED34S L1500 version)
	6000 lm (LED60S L1500 version)
Correlated Color	4000 K
Temperature	
Color Rendering Index	≥ 80
Lumen maintenance at median useful life*	L75
50000 h	
Control gear failure rate at median useful life	5%
50000 h	
Performance Ambient Temperature Tq	+25 °C

Operating temperature range	-20 to +35 °C
Driver	Built-in, replaceable
Mains voltage	220-240V / 50-60 Hz
Dimming	DALI
	Wireless Dim
Material	Housing: injection molded polycarbonate
	Diffuser: injection molded polycarbonate
	Closing clips: stainless spring steel
Color	Grey (RAL 7035)
Optical cover	Polycarbonate, clear with texture applied at the inside
Connection	Internal push-in connection with cable gland
	Optional: Waterproof External Connector (WEC) for easier installation
Maintenance	No internal cleaning required
Installation	Fixation with ceiling mounted bracket
	(vandal-proof by additional screw fixation)
	Through-wiring possible
	Suspension possible
Options	After electrical installation in housing luminaire is closed by optical cover and closing clips
	Emergency lighting 3 hours duration
Remarks	All mounting accessories are included

CoreLine Waterproof

Versions



CoreLine Waterproof WT120C luminaire



Coreline Waterproof



Coreline Waterproof G2 LSC - LED Module, system flux 2700 lm - 840 neutral white - Power supply unit



840 neutral white - Power supply unit

Product details



Stainless spring steel clips for fast closing of the luminaire



Electrical connection between LED driver and diffuser with integrated LED source



Ceiling bracket and anti-vandal screws



Extra cable gland and stopper

Product details



Easy installation



Easy installation



Easy installation



Ceiling bracket and anti-vandal screws



Ceiling bracket with suspension and anti-vandal screws



LED module integrated in the cover



Side view



Front view

CoreLine Waterproof

Product details



Close up anti-vandal screw



CoreLine_Waterproof_DOB-
DP01.tif



CoreLine_Waterproof_DOB-
DP02.tif



CoreLine Waterproof WT120C G2
PCU-7DPP



CoreLine Waterproof WT120C G2
PCU-3DPP



CoreLine Waterproof WT120C G2
PCU-10DPP



CoreLine Waterproof WT120C G2
PCU-9DPP




CoreLine Waterproof WT120C G2
PCU-12DPP


CoreLine Waterproof

Product details

CoreLine Waterproof WT120C G2
PCU-2DPP



CoreLine Waterproof WT120C G2
PCU-13DPP



CoreLine Waterproof WT120C G2
PCU-8DPP



CoreLine Waterproof WT120C G2
PCU-11DPP



Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

General Information

CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit

Initial Performance (IEC Compliant)

Init. Corr. Color Temperature	4000 K
Luminous flux tolerance	+/-10%

Mechanical and Housing

Color	Gray
-------	------

Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500453335	WT120C LED18S/840 PSU L600	-20 to +35 °C	Not applicable	Yes
910500453336	WT120C LED22S/840 PSU L1200	-20 to +35 °C	Not applicable	Yes
910500453337	WT120C LED34S/840 PSU L1500	-20 to +35 °C	Not applicable	Yes
910500453338	WT120C LED40S/840 PSU L1200	-20 to +35 °C	Not applicable	Yes
910500453339	WT120C LED60S/840 PSU L1500	-20 to +35 °C	Not applicable	Yes
910500454298	WT120C LED22S/840 PSU L1200 EL1	0 to +25 °C	Not applicable	Yes
910500454299	WT120C LED40S/840 PSU L1200 EL1	0 to +25 °C	Not applicable	Yes
910500454301	WT120C LED34S/840 PSU L1500 EL1	0 to +25 °C	Not applicable	Yes
910500454302	WT120C LED60S/840 PSU L1500 EL1	0 to +25 °C	Not applicable	Yes
910500454303	WT120C LED22S/840 PSU L1200 EL3	0 to +25 °C	Not applicable	Yes
910500454304	WT120C LED40S/840 PSU L1200 EL3	0 to +25 °C	Not applicable	Yes
910500454305	WT120C LED34S/840 PSU L1500 EL3	0 to +25 °C	Not applicable	Yes

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500454306	WT120C LED60S/840 PSU L1500 EL3	0 to +25 °C	Not applicable	Yes
910500458243	WT120C LED18S/840 PSD L600	-25 to +35 °C	1%	Yes
910500458244	WT120C LED22S/840 PSD L1200	-25 to +35 °C	1%	Yes
910500458245	WT120C LED34S/840 PSD L1500	-25 to +35 °C	1%	Yes
910500458246	WT120C LED40S/840 PSD L1200	-25 to +35 °C	1%	Yes
910500458247	WT120C LED60S/840 PSD L1500	-25 to +35 °C	1%	Yes
910500458248	WT120C LED22S/840 PSD L1200 EL3	0 to +25 °C	1%	Yes
910500458249	WT120C LED40S/840 PSD L1200 EL3	0 to +25 °C	1%	Yes
910500458250	WT120C LED34S/840 PSD L1500 EL3	0 to +25 °C	1%	Yes
910500458251	WT120C LED60S/840 PSD L1500 EL3	0 to +25 °C	1%	Yes
910500458794	WT120C LED22S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable	Yes
910500458795	WT120C LED34S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Yes
910500458796	WT120C LED40S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable	Yes
910500458797	WT120C LED60S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Yes
910500465266	WT120C LED40S/840 IA1 L1200	-20 to +35 °C	-	Yes
910500465267	WT120C LED60S/840 IA1 L1500	-20 to +35 °C	-	Yes
910500465326	WT120C LED40S/840 IA1 L1200 EL3	0 to +25 °C	1%	Yes
910500465327	WT120C LED60S/840 IA1 L1500 EL3	0 to +25 °C	1%	Yes
910500465651	WT120C LED80S/840 PSU L1500	-25 to +35 °C	Not applicable	Yes
910500465652	WT120C LED80S/840 PSD L1500	-25 to +35 °C	1%	Yes
910500465653	WT120C LED80S/840 PSU TW3 L1500	-25 to +35 °C	Not applicable	Yes
910500465654	WT120C LED80S/840 PSU L1500 EL3	0 to +25 °C	Not applicable	Yes
910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C	Not applicable	Yes
910500459302	WT120C LED60S/840 PSU WEC L1500	-20 to +35 °C	Not applicable	Yes
910505100038	WT120C G2 LED19S/840 PSD L600	-10 to +35 °C	1%	-
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-10 to +35 °C	Not applicable	-

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable	-
910505100044	WT120C G2 LED27S/840 PSD L1200	-10 to +35 °C	1%	-
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C	1%	-
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-10 to +35 °C	Not applicable	-
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-10 to +35 °C	Not applicable	-
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-10 to +35 °C	Not applicable	-
910505100052	WT120C G2 LED40S/840 IA1 L1200	-10 to +35 °C	10%	-
910505100053	WT120C G2 LED40S/840 PSD L1200	-10 to +35 °C	1%	-
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable	-
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	0 to +25 °C	10%	-
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C	1%	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-10 to +35 °C	Not applicable	-
910505100061	WT120C G2 LED34S/840 PSD L1500	-10 to +35 °C	1%	-
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable	-
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C	1%	-
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-10 to +35 °C	Not applicable	-
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-10 to +35 °C	Not applicable	-
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-10 to +35 °C	Not applicable	-
910505100071	WT120C G2 LED60S/840 IA1 L1500	-10 to +35 °C	10%	-
910505100072	WT120C G2 LED60S/840 PSD L1500	-10 to +35 °C	1%	-
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable	-
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	0 to +25 °C	10%	-
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	0 to +25 °C	1%	-
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-10 to +35 °C	Not applicable	-
910505100079	WT120C G2 LED80S/840 PSD L1500	-10 to +35 °C	1%	-

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C	Not applicable	-
911401823480	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C	Not applicable	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C	Not applicable	-
911401823680	WT120C G2 LED34S/840 PSU L1500	-20 to +40 °C	Not applicable	-
911401823780	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C	Not applicable	-
911401823880	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C	Not applicable	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C	Not applicable	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C	Not applicable	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-20 to +40 °C	Not applicable	-
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C	Not applicable	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	-

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910500453335	WT120C LED18S/840 PSU L600	No	910500458250	WT120C LED34S/840 PSD L1500 EL3	Yes
910500453336	WT120C LED22S/840 PSU L1200	No	910500458251	WT120C LED60S/840 PSD L1500 EL3	Yes
910500453337	WT120C LED34S/840 PSU L1500	No	910500458794	WT120C LED22S/840 PSU TW3 L1200	No
910500453338	WT120C LED40S/840 PSU L1200	No	910500458795	WT120C LED34S/840 PSU TW3 L1500	No
910500453339	WT120C LED60S/840 PSU L1500	No	910500458796	WT120C LED40S/840 PSU TW3 L1200	No
910500454298	WT120C LED22S/840 PSU L1200 EL1	No	910500458797	WT120C LED60S/840 PSU TW3 L1500	No
910500454299	WT120C LED40S/840 PSU L1200 EL1	No	910500465266	WT120C LED40S/840 IA1 L1200	Wireless Dim
910500454301	WT120C LED34S/840 PSU L1500 EL1	No	910500465267	WT120C LED60S/840 IA1 L1500	Wireless Dim
910500454302	WT120C LED60S/840 PSU L1500 EL1	No	910500465326	WT120C LED40S/840 IA1 L1200 EL3	Yes
910500454303	WT120C LED22S/840 PSU L1200 EL3	No	910500465327	WT120C LED60S/840 IA1 L1500 EL3	Yes
910500454304	WT120C LED40S/840 PSU L1200 EL3	No	910500465651	WT120C LED80S/840 PSU L1500	No
910500454305	WT120C LED34S/840 PSU L1500 EL3	No	910500465652	WT120C LED80S/840 PSD L1500	Yes
910500454306	WT120C LED60S/840 PSU L1500 EL3	No	910500465653	WT120C LED80S/840 PSU TW3 L1500	No
910500458243	WT120C LED18S/840 PSD L600	Yes	910500465654	WT120C LED80S/840 PSU L1500 EL3	No
910500458244	WT120C LED22S/840 PSD L1200	Yes	910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	No
910500458245	WT120C LED34S/840 PSD L1500	Yes	910500459302	WT120C LED60S/840 PSU WEC L1500	No
910500458246	WT120C LED40S/840 PSD L1200	Yes	910505100038	WT120C G2 LED19S/840 PSD L600	Yes
910500458247	WT120C LED60S/840 PSD L1500	Yes	910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	No
910500458248	WT120C LED22S/840 PSD L1200 EL3	Yes	910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	No
910500458249	WT120C LED40S/840 PSD L1200 EL3	Yes	910505100044	WT120C G2 LED27S/840 PSD L1200	Yes

CoreLine Waterproof

Order Code	Full Product Name	Dimmable
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	No
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	No
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No
910505100052	WT120C G2 LED40S/840 IA1 L1200	Wireless Dim
910505100053	WT120C G2 LED40S/840 PSD L1200	Yes
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	No
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	Wireless Dim
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	No
910505100061	WT120C G2 LED34S/840 PSD L1500	Yes
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	No
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	No
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	No
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No
910505100071	WT120C G2 LED60S/840 IA1 L1500	Wireless Dim
910505100072	WT120C G2 LED60S/840 PSD L1500	Yes

Order Code	Full Product Name	Dimmable
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	No
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	Wireless Dim
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	No
910505100079	WT120C G2 LED80S/840 PSD L1500	Yes
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	No
911401823480	WT120C G2 LED19S/840 PSU L600	No
911401823580	WT120C G2 LED27S/840 PSU L1200	No
911401823680	WT120C G2 LED34S/840 PSU L1500	No
911401823780	WT120C G2 LED40S/840 PSU L1200	No
911401823880	WT120C G2 LED60S/840 PSU L1500	No
911401823980	WT120C G2 LED80S/840 PSU L1500	No
911401836980	WT120C G2 LED18S/840 PSU PCO L600	No
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	No
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	No
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	No
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	No
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	No

Operating and Electrical

Order Code	Full Product Name	Input Voltage
910500453335	WT120C LED18S/840 PSU L600	220 to 240 V
910500453336	WT120C LED22S/840 PSU L1200	220 to 240 V
910500453337	WT120C LED34S/840 PSU L1500	220 to 240 V
910500453338	WT120C LED40S/840 PSU L1200	220 to 240 V
910500453339	WT120C LED60S/840 PSU L1500	220 to 240 V
910500454298	WT120C LED22S/840 PSU L1200 EL1	220 to 240 V
910500454299	WT120C LED40S/840 PSU L1200 EL1	220 to 240 V
910500454301	WT120C LED34S/840 PSU L1500 EL1	220 to 240 V
910500454302	WT120C LED60S/840 PSU L1500 EL1	220 to 240 V
910500454303	WT120C LED22S/840 PSU L1200 EL3	220 to 240 V
910500454304	WT120C LED40S/840 PSU L1200 EL3	220 to 240 V
910500454305	WT120C LED34S/840 PSU L1500 EL3	220 to 240 V
910500454306	WT120C LED60S/840 PSU L1500 EL3	220 to 240 V
910500458243	WT120C LED18S/840 PSD L600	220 to 240 V
910500458244	WT120C LED22S/840 PSD L1200	220 to 240 V
910500458245	WT120C LED34S/840 PSD L1500	220 to 240 V
910500458246	WT120C LED40S/840 PSD L1200	220 to 240 V
910500458247	WT120C LED60S/840 PSD L1500	220 to 240 V
910500458248	WT120C LED22S/840 PSD L1200 EL3	220 to 240 V
910500458249	WT120C LED40S/840 PSD L1200 EL3	220 to 240 V
910500458250	WT120C LED34S/840 PSD L1500 EL3	220 to 240 V
910500458251	WT120C LED60S/840 PSD L1500 EL3	220 to 240 V
910500458794	WT120C LED22S/840 PSU TW3 L1200	220–240 V
910500458795	WT120C LED34S/840 PSU TW3 L1500	220–240 V
910500458796	WT120C LED40S/840 PSU TW3 L1200	220–240 V
910500458797	WT120C LED60S/840 PSU TW3 L1500	220–240 V
910500465266	WT120C LED40S/840 IA1 L1200	220 to 240 V
910500465267	WT120C LED60S/840 IA1 L1500	220 to 240 V
910500465326	WT120C LED40S/840 IA1 L1200 EL3	220 to 240 V
910500465327	WT120C LED60S/840 IA1 L1500 EL3	220 to 240 V

Order Code	Full Product Name	Input Voltage
910500465651	WT120C LED80S/840 PSU L1500	220 to 240 V
910500465652	WT120C LED80S/840 PSD L1500	220 to 240 V
910500465653	WT120C LED80S/840 PSU TW3 L1500	220 to 240 V
910500465654	WT120C LED80S/840 PSU L1500 EL3	220 to 240 V
910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	220 to 240 V
910500459302	WT120C LED60S/840 PSU WEC L1500	220 to 240 V
910505100038	WT120C G2 LED19S/840 PSD L600	220 to 240 V
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	220 to 240 V
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	220 to 240 V
910505100044	WT120C G2 LED27S/840 PSD L1200	220 to 240 V
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	220 to 240 V
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	220 to 240 V
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	220 to 240 V
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	220 to 240 V
910505100052	WT120C G2 LED40S/840 IA1 L1200	220 to 240 V
910505100053	WT120C G2 LED40S/840 PSD L1200	220 to 240 V
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	220 to 240 V
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	220 to 240 V
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	220 to 240 V
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	220 to 240 V
910505100061	WT120C G2 LED34S/840 PSD L1500	220 to 240 V
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	220 to 240 V
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	220 to 240 V
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	220 to 240 V
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	220 to 240 V
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	220 to 240 V
910505100071	WT120C G2 LED60S/840 IA1 L1500	220 to 240 V
910505100072	WT120C G2 LED60S/840 PSD L1500	220 to 240 V
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	220 to 240 V
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	220 to 240 V

CoreLine Waterproof

Order Code	Full Product Name	Input Voltage
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	220 to 240 V
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	220 to 240 V
910505100079	WT120C G2 LED80S/840 PSD L1500	220 to 240 V
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	220 to 240 V
911401823480	WT120C G2 LED19S/840 PSU L600	220 to 240 V
911401823580	WT120C G2 LED27S/840 PSU L1200	220 to 240 V
911401823680	WT120C G2 LED34S/840 PSU L1500	220 to 240 V
911401823780	WT120C G2 LED40S/840 PSU L1200	220 to 240 V

Order Code	Full Product Name	Input Voltage
911401823880	WT120C G2 LED60S/840 PSU L1500	220 to 240 V
911401823980	WT120C G2 LED80S/840 PSU L1500	220 to 240 V
911401836980	WT120C G2 LED18S/840 PSU PCO L600	220 to 240 V
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	220 to 240 V
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	220 to 240 V
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	220 to 240 V
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	220 to 240 V
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	220 to 240 V

General Information (1/2)

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/ lens type	Emergency lighting
910500453335	WT120C LED18S/840 PSU L600	-	-	Polycarbonate bowl/cover	-
910500453336	WT120C LED22S/840 PSU L1200	-	-	Polycarbonate bowl/cover	-
910500453337	WT120C LED34S/840 PSU L1500	-	-	Polycarbonate bowl/cover	-
910500453338	WT120C LED40S/840 PSU L1200	120 °	-	Polycarbonate bowl/cover	-
910500453339	WT120C LED60S/840 PSU L1500	120 °	-	Polycarbonate bowl/cover	-
910500454298	WT120C LED22S/840 PSU L1200 EL1	-	-	Polycarbonate bowl/cover	Emergency lighting 1 hour duration
910500454299	WT120C LED40S/840 PSU L1200 EL1	-	-	Polycarbonate bowl/cover	Emergency lighting 1 hour duration
910500454301	WT120C LED34S/840 PSU L1500 EL1	-	-	Polycarbonate bowl/cover	Emergency lighting 1 hour duration
910500454302	WT120C LED60S/840 PSU L1500 EL1	-	-	Polycarbonate bowl/cover	Emergency lighting 1 hour duration
910500454303	WT120C LED22S/840 PSU L1200 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration
910500454304	WT120C LED40S/840 PSU L1200 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/ lens type	Emergency lighting
910500454305	WT120C LED34S/840 PSU L1500 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration
910500454306	WT120C LED60S/840 PSU L1500 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration
910500458243	WT120C LED18S/840 PSD L600	-	-	Polycarbonate bowl/cover	-
910500458244	WT120C LED22S/840 PSD L1200	-	-	Polycarbonate bowl/cover	-
910500458245	WT120C LED34S/840 PSD L1500	-	-	Polycarbonate bowl/cover	-
910500458246	WT120C LED40S/840 PSD L1200	-	-	Polycarbonate bowl/cover	-
910500458247	WT120C LED60S/840 PSD L1500	-	-	Polycarbonate bowl/cover	-
910500458248	WT120C LED22S/840 PSD L1200 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration
910500458249	WT120C LED40S/840 PSD L1200 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration
910500458250	WT120C LED34S/840 PSD L1500 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration

CoreLine Waterproof

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/ lens type	Emergency lighting
910500458251	WT120C LED60S/840 PSD L1500 EL3	-	-	Polycarbonate bowl/cover	Emergency lighting 3 hours duration
910500458794	WT120C LED22S/840 PSU TW3 L1200	120 °	-	-	-
910500458795	WT120C LED34S/840 PSU TW3 L1500	120 °	-	-	-
910500458796	WT120C LED40S/840 PSU TW3 L1200	120 °	-	-	-
910500458797	WT120C LED60S/840 PSU TW3 L1500	120 °	-	-	-
910500465266	WT120C LED40S/840 IA1 L1200	120 °	-	-	-
910500465267	WT120C LED60S/840 IA1 L1500	120 °	-	-	-
910500465326	WT120C LED40S/840 IA1 L1200 EL3	-	-	-	-
910500465327	WT120C LED60S/840 IA1 L1500 EL3	-	-	-	-
910500465651	WT120C LED80S/840 PSU L1500	120 °	-	-	-
910500465652	WT120C LED80S/840 PSD L1500	120 °	-	-	-
910500465653	WT120C LED80S/840 PSU TW3 L1500	120 °	-	-	-
910500465654	WT120C LED80S/840 PSU L1500 EL3	120 °	-	-	Emergency lighting 3 hours duration
910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	-	-	-	-
910500459302	WT120C LED60S/840 PSU WEC L1500	-	-	-	-

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/ lens type	Emergency lighting
910505100038	WT120C G2 LED19S/840 PSD L600	-	-	-	-
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	-	-	-
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	-	-	-	-
910505100044	WT120C G2 LED27S/840 PSD L1200	-	-	-	-
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	-	-	-	-
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	-	-	-
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-	-	-	-
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	-	-	-
910505100052	WT120C G2 LED40S/840 IA1 L1200	-	-	-	-
910505100053	WT120C G2 LED40S/840 PSD L1200	-	-	-	-
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	-	-	-	-
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	-	-	-
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	-	-	-	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	-	-	-
910505100061	WT120C G2 LED34S/840 PSD L1500	-	-	-	-
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	-	-	-	-

CoreLine Waterproof

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/ lens type	Emergency lighting
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	-	-	-	-
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	-	-	-
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	-	-	-
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	-	-	-
910505100071	WT120C G2 LED60S/840 IA1 L1500	-	-	-	-
910505100072	WT120C G2 LED60S/840 PSD L1500	-	-	-	-
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	-	-	-	-
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	-	-	-
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	-	-	-	-
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	-	-	-
910505100079	WT120C G2 LED80S/840 PSD L1500	-	-	-	-
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	-	-	-	-

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/ lens type	Emergency lighting
911401823480	WT120C G2 LED19S/840 PSU L600	- °	-	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	- °	-	-	-
911401823680	WT120C G2 LED34S/840 PSU L1500	- °	-	-	-
911401823780	WT120C G2 LED40S/840 PSU L1200	- °	-	-	-
911401823880	WT120C G2 LED60S/840 PSU L1500	- °	-	-	-
911401823980	WT120C G2 LED80S/840 PSU L1500	- °	-	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	- °	-	-	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	- °	-	-	-
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	- °	-	-	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	- °	-	-	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	- °	-	-	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	- °	-	-	-

General Information (2/2)

Order Code	Full Product Name	Gear	Lamp family code	Number of light sources	Optic type	Product Family Code	UL mark
910500453335	WT120C LED18S/840 PSU L600	-	-	1 pc	-	WT120C	-
910500453336	WT120C LED22S/840 PSU L1200	-	-	1 pc	-	WT120C	-
910500453337	WT120C LED34S/840 PSU L1500	-	-	1 pc	-	WT120C	-
910500453338	WT120C LED40S/840 PSU L1200	-	-	1 pc	-	WT120C	-
910500453339	WT120C LED60S/840 PSU L1500	-	-	1 pc	-	WT120C	-
910500454298	WT120C LED22S/840 PSU L1200 EL1	-	-	1 pc	-	WT120C	-
910500454299	WT120C LED40S/840 PSU L1200 EL1	-	-	1 pc	-	WT120C	-
910500454301	WT120C LED34S/840 PSU L1500 EL1	-	-	1 pc	-	WT120C	-
910500454302	WT120C LED60S/840 PSU L1500 EL1	-	-	1 pc	-	WT120C	-

CoreLine Waterproof

Order Code	Full Product Name	Gear	Lamp family code	Number of light sources	Optic type	Product Family Code	UL mark
910500454303	WT120C LED22S/840 PSU L1200 EL3	-	-	1 pc	-	WT120C	-
910500454304	WT120C LED40S/840 PSU L1200 EL3	-	-	1 pc	-	WT120C	-
910500454305	WT120C LED34S/840 PSU L1500 EL3	-	-	1 pc	-	WT120C	-
910500454306	WT120C LED60S/840 PSU L1500 EL3	-	-	1 pc	-	WT120C	-
910500458243	WT120C LED18S/840 PSD L600	-	-	1 pc	-	WT120C	-
910500458244	WT120C LED22S/840 PSD L1200	-	-	1 pc	-	WT120C	-
910500458245	WT120C LED34S/840 PSD L1500	-	-	1 pc	-	WT120C	-
910500458246	WT120C LED40S/840 PSD L1200	-	-	1 pc	-	WT120C	-
910500458247	WT120C LED60S/840 PSD L1500	-	-	1 pc	-	WT120C	-
910500458248	WT120C LED22S/840 PSD L1200 EL3	-	-	1 pc	-	WT120C	-
910500458249	WT120C LED40S/840 PSD L1200 EL3	-	-	1 pc	-	WT120C	-
910500458250	WT120C LED34S/840 PSD L1500 EL3	-	-	1 pc	-	WT120C	-
910500458251	WT120C LED60S/840 PSD L1500 EL3	-	-	1 pc	-	WT120C	-
910500458794	WT120C LED22S/840 PSU TW3 L1200	-	-	1 pc	-	WT120C	-
910500458795	WT120C LED34S/840 PSU TW3 L1500	-	-	1 pc	-	WT120C	-
910500458796	WT120C LED40S/840 PSU TW3 L1200	-	-	1 pc	-	WT120C	-
910500458797	WT120C LED60S/840 PSU TW3 L1500	-	-	1 pc	-	WT120C	-
910500465266	WT120C LED40S/840 IA1 L1200	-	-	-	-	WT120C	-
910500465267	WT120C LED60S/840 IA1 L1500	-	-	-	-	WT120C	-
910500465326	WT120C LED40S/840 IA1 L1200 EL3	-	-	-	-	WT120C	-
910500465327	WT120C LED60S/840 IA1 L1500 EL3	-	-	-	-	WT120C	-
910500465651	WT120C LED80S/840 PSU L1500	-	-	-	-	WT120C	-
910500465652	WT120C LED80S/840 PSD L1500	-	-	-	-	WT120C	-
910500465653	WT120C LED80S/840 PSU TW3 L1500	-	-	-	-	WT120C	-
910500465654	WT120C LED80S/840 PSU L1500 EL3	-	-	-	-	WT120C	-
910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	-	-	-	-	WT120C	-
910500459302	WT120C LED60S/840 PSU WEC L1500	-	-	-	-	WT120C	-
910505100038	WT120C G2 LED19S/840 PSD L600	-	-	-	Beam angle 110°	WT130C	-
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100044	WT120C G2 LED27S/840 PSD L1200	-	-	-	Beam angle 110°	WT130C	-
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-	-	-	Beam angle 110°	WT130C	-
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	-	-	Beam angle 110°	WT130C	-
910505100052	WT120C G2 LED40S/840 IA1 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100053	WT120C G2 LED40S/840 PSD L1200	-	-	-	Beam angle 110°	WT130C	-
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	-	-	-	Beam angle 110°	WT130C	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100061	WT120C G2 LED34S/840 PSD L1500	-	-	-	Beam angle 110°	WT130C	-
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	-	-	Beam angle 110°	WT130C	-
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	-	-	Beam angle 110°	WT130C	-
910505100071	WT120C G2 LED60S/840 IA1 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100072	WT120C G2 LED60S/840 PSD L1500	-	-	-	Beam angle 110°	WT130C	-
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	-	-	-	Beam angle 110°	WT130C	-

CoreLine Waterproof

Order Code	Full Product Name	Gear	Lamp family code	Number of light sources	Optic type	Product Family Code	UL mark
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	-	-	Beam angle 110°	WT130C	-
910505100079	WT120C G2 LED80S/840 PSD L1500	-	-	-	Beam angle 110°	WT130C	-
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	-	-	-	Beam angle 110°	WT130C	-
911401823480	WT120C G2 LED19S/840 PSU L600	-	-	-	Beam angle 110°	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-	-	-	Beam angle 110°	-	-
911401823680	WT120C G2 LED34S/840 PSU L1500	-	-	-	Beam angle 110°	-	-
911401823780	WT120C G2 LED40S/840 PSU L1200	-	-	-	Beam angle 110°	-	-
911401823880	WT120C G2 LED60S/840 PSU L1500	-	-	-	Beam angle 110°	-	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-	-	-	Beam angle 110°	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-	-	-	Beam angle 110°	-	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-	-	-	Beam angle 110°	-	-
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-	-	-	Beam angle 110°	-	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-	-	-	Beam angle 110°	-	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-	-	-	Beam angle 110°	-	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-	-	-	Beam angle 110°	-	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
910500453335	WT120C LED18S/84 0 PSU L600	(0.38, 0.38) SDCM <3	≥80	119 lm/W	2100 lm
910500453336	WT120C LED22S/84 0 PSU L1200	(0.38, 0.38) SDCM <3	≥80	123 lm/W	2900 lm
910500453337	WT120C LED34S/84 0 PSU L1500	(0.38, 0.38) SDCM <3	≥80	119 lm/W	3500 lm
910500453338	WT120C LED40S/84 0 PSU L1200	(0.38, 0.38) SDCM <3	≥80	115 lm/W	4100 lm
910500453339	WT120C LED60S/84 0 PSU L1500	(0.38, 0.38) SDCM <3	≥80	125 lm/W	6000 lm
910500454298	WT120C LED22S/84 0 PSU L1200 EL1	(0.38, 0.38) SDCM <3	≥80	98 lm/W	2900 lm
910500454299	WT120C LED40S/84 0 PSU L1200 EL1	(0.38, 0.38) SDCM <3	≥80	104 lm/W	4100 lm
910500454301	WT120C LED34S/84	(0.38, 0.38) SDCM <3	≥80	106 lm/W	3500 lm

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
910500454302	0 PSU L1500 EL1	(0.38, 0.38) SDCM <3	≥80	115 lm/W	6000 lm
910500454303	WT120C LED22S/84 0 PSU L1200 EL3	(0.38, 0.38) SDCM <3	≥80	98 lm/W	2900 lm
910500454304	WT120C LED40S/84 0 PSU L1200 EL3	(0.38, 0.38) SDCM <3	≥80	104 lm/W	4100 lm
910500454305	WT120C LED34S/84 0 PSU L1500 EL3	(0.38, 0.38) SDCM <3	≥80	106 lm/W	3500 lm
910500454306	WT120C LED60S/84 0 PSU L1500 EL3	(0.38, 0.38) SDCM <3	≥80	115 lm/W	6000 lm
910500458243	WT120C LED18S/84 0 PSD L600	(0.38, 0.38) SDCM <3	≥80	114 lm/W	2100 lm
910500458244	WT120C LED22S/84 0 PSD L1200	(0.38, 0.38) SDCM <3	≥80	118 lm/W	2900 lm

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
910500458245	WT120C LED34S/84 0 PSD L1500	(0.38, 0.38) SDCM <3	≥80	117 lm/W	3500 lm
910500458246	WT120C LED40S/84 0 PSD L1200	(0.38, 0.38) SDCM <3	≥80	112 lm/W	4100 lm
910500458247	WT120C LED60S/84 0 PSD L1500	(0.38, 0.38) SDCM <3	≥80	121 lm/W	6000 lm
910500458248	WT120C LED22S/84 0 PSD L1200 EL3	(0.38, 0.38) SDCM <3	≥80	98 lm/W	2900 lm
910500458249	WT120C LED40S/84 0 PSD L1200 EL3	(0.38, 0.38) SDCM <3	≥80	104 lm/W	4100 lm
910500458250	WT120C LED34S/84 0 PSD L1500 EL3	(0.38, 0.38) SDCM <3	≥80	106 lm/W	3500 lm
910500458251	WT120C LED60S/84 0 PSD L1500 EL3	(0.38, 0.38) SDCM <3	≥80	115 lm/W	6000 lm
910500458794	WT120C LED22S/84 0 PSU TW3 L1200	(0.38, 0.38) SDCM <3	≥80	123 lm/W	2900 lm
910500458795	WT120C LED34S/84 0 PSU TW3 L1500	(0.38, 0.38) SDCM <3	≥80	119 lm/W	3500 lm
910500458796	WT120C LED40S/84 0 PSU TW3 L1200	(0.38, 0.38) SDCM <3	≥80	115 lm/W	4100 lm
910500458797	WT120C LED60S/84 0 PSU TW3 L1500	(0.38, 0.38) SDCM <3	≥80	125 lm/W	6000 lm
910500465266	WT120C LED40S/84 0 IA1 L1200	(0.38, 0.38) SDCM <3	≥80	112 lm/W	4100 lm
910500465267	WT120C LED60S/84 0 IA1 L1500	(0.38, 0.38) SDCM <3	≥80	121 lm/W	6000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
910500465326	WT120C LED40S/84 0 IA1 L1200 EL3	(0.38, 0.38) SDCM <3	≥80	104 lm/W	4100 lm
910500465327	WT120C LED60S/84 0 IA1 L1500 EL3	(0.38, 0.38) SDCM <3	≥80	115 lm/W	6000 lm
910500465651	WT120C LED80S/84 0 PSU L1500	(0.38, 0.38) SDCM <3	≥80	118 lm/W	8000 lm
910500465652	WT120C LED80S/84 0 PSD L1500	(0.38, 0.38) SDCM <3	≥80	118 lm/W	8000 lm
910500465653	WT120C LED80S/84 0 PSU TW3 L1500	(0.38, 0.38) SDCM <3	≥80	118 lm/W	8000 lm
910500465654	WT120C LED80S/84 0 PSU L1500 EL3	(0.38, 0.38) SDCM <3	≥80	113 lm/W	8000 lm
910500459301	WT120C LED40S/84 0 PSU TW1 WEC L1200	(0.38, 0.38) SDCM <3	≥80	125 lm/W	4000 lm
910500459302	WT120C LED60S/84 0 PSU WEC L1500	(0.38, 0.38) SDCM <3	≥80	125 lm/W	6000 lm
910505100038	WT120C G2 LED19S/84 0 PSD L600	(0.43, 0.40) SDCM <3	>80	118.75 lm/W	1900 lm
910505100039	WT120C G2 LED27S/84 0 PSU TW3 L1200	(0.43, 0.40) SDCM <3	>80	128.57 lm/W	2700 lm
910505100042	WT120C G2 LED27S/84 0 PSU ELB3 L1200	(0.43, 0.40) SDCM <3	>80	103.85 lm/W	2700 lm
910505100044	WT120C G2 LED27S/84 0 PSD L1200	(0.43, 0.40) SDCM <3	>80	122.73 lm/W	2700 lm
910505100045	WT120C G2 LED27S/84	(0.43, 0.40) SDCM <3	>80	100 lm/W	2700 lm

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
	0 PSD ELB3 L1200				
910505100047	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	4000 lm
	0 PSU TW3 L1200				
910505100050	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	4000 lm
	0 PSU WEC L1200				
910505100051	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	4000 lm
	0 PSU TW1 WEC L1200				
910505100052	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	4000 lm
	0 IA1 L1200				
910505100053	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	4000 lm
	0 PSD L1200				
910505100054	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	114.29 lm/W	4000 lm
	0 PSU ELB3 L1200				
910505100056	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	115.94 lm/W	4000 lm
	0 IA1 ELB3 L1200				
910505100057	WT120C G2 LED40S/84	(0.43, 0.40) SDCM <3	>80	114.29 lm/W	4000 lm
	0 PSD ELB3 L1200				
910505100058	WT120C G2 LED34S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	3400 lm
	0 PSU TW3 L1500				
910505100061	WT120C G2 LED34S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	3400 lm
	0 PSD L1500				
910505100062	WT120C G2 LED34S/84	(0.43, 0.40) SDCM <3	>80	111.48 lm/W	3400 lm
	0 PSU ELB3 L1500				
910505100064	WT120C G2 LED34S/84	(0.43, 0.40) SDCM <3	>80	111.48 lm/W	3400 lm
	0 PSD ELB3 L1500				

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
910505100066	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	6000 lm
	0 PSU TW3 L1500				
910505100069	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	6000 lm
	0 PSU WEC L1500				
910505100070	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	6000 lm
	0 PSU TW1 WEC L1500				
910505100071	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	131.87 lm/W	6000 lm
	0 IA1 L1500				
910505100072	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	133.33 lm/W	6000 lm
	0 PSD L1500				
910505100073	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	120 lm/W	6000 lm
	0 PSU ELB3 L1500				
910505100075	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	120 lm/W	6000 lm
	0 IA1 ELB3 L1500				
910505100076	WT120C G2 LED60S/84	(0.43, 0.40) SDCM <3	>80	117.65 lm/W	6000 lm
	0 PSD ELB3 L1500				
910505100077	WT120C G2 LED80S/84	(0.43, 0.40) SDCM <3	>80	131.15 lm/W	8000 lm
	0 PSU TW3 L1500				
910505100079	WT120C G2 LED80S/84	(0.43, 0.40) SDCM <3	>80	131.15 lm/W	8000 lm
	0 PSD L1500				
910505100080	WT120C G2 LED80S/84	(0.43, 0.40) SDCM <3	>80	121.21 lm/W	8000 lm
	0 PSU L1500 ELB3				
911401823480	WT120C G2 LED19S/84	(0.38, 0.38) SDCM <=3	>80	126.67 lm/W	1900 lm
	0 PSU L600				
911401823580	WT120C G2 LED27S/84	(0.38, 0.38) SDCM <=3	>80	131.71 lm/W	2700 lm

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticy	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
	0 PSU L1200				
911401823680	WT120C G2 LED34S/84	(0.38,0.38)SDCM<=3	>80	139.92 lm/W	3400 lm
	0 PSU L1500				
911401823780	WT120C G2 LED40S/84	(0.38,0.38)SDCM<=3	>80	139.86 lm/W	4000 lm
	0 PSU L1200				
911401823880	WT120C G2 LED60S/84	(0.38,0.38)SDCM<=3	>80	139.86 lm/W	6000 lm
	0 PSU L1500				
911401823980	WT120C G2 LED80S/84	(0.38,0.38)SDCM<=3	>80	140.11 lm/W	8000 lm
	0 PSU L1500				
911401836980	WT120C G2 LED18S/84	(0.38,0.38)SDCM<=3	>80	120 lm/W	1800 lm

Order Code	Full Product Name	Initial chromaticy	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
	0 PSU PCO L600				
911401837080	WT120C G2 LED25S/84	(0.38,0.38)SDCM<=3	>80	121.95 lm/W	2500 lm
	0 PSU PCO L1200				
911401837180	WT120C G2 LED31S/84	(0.38,0.38)SDCM<=3	>80	127.57 lm/W	3100 lm
	0 PSU PCO L1500				
911401837280	WT120C G2 LED37S/84	(0.38,0.38)SDCM<=3	>80	129.37 lm/W	3700 lm
	0 PSU PCO L1200				
911401837380	WT120C G2 LED57S/84	(0.38,0.38)SDCM<=3	>80	132.87 lm/W	5700 lm
	0 PSU PCO L1500				
911401837480	WT120C G2 LED75S/84	(0.38,0.38)SDCM<=3	>80	131.35 lm/W	7500 lm
	0 PSU PCO L1500				

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910500453335	WT120C LED18S/840 PSU L600	17.6 W
910500453336	WT120C LED22S/840 PSU L1200	23.5 W
910500453337	WT120C LED34S/840 PSU L1500	29.5 W
910500453338	WT120C LED40S/840 PSU L1200	35.5 W
910500453339	WT120C LED60S/840 PSU L1500	48 W
910500454298	WT120C LED22S/840 PSU L1200 EL1	22.5 W
910500454299	WT120C LED40S/840 PSU L1200 EL1	39.5 W
910500454301	WT120C LED34S/840 PSU L1500 EL1	33 W
910500454302	WT120C LED60S/840 PSU L1500 EL1	52 W
910500454303	WT120C LED22S/840 PSU L1200 EL3	22.5 W
910500454304	WT120C LED40S/840 PSU L1200 EL3	39.5 W
910500454305	WT120C LED34S/840 PSU L1500 EL3	33 W
910500454306	WT120C LED60S/840 PSU L1500 EL3	52 W
910500458243	WT120C LED18S/840 PSD L600	18.5 W
910500458244	WT120C LED22S/840 PSD L1200	24.5 W
910500458245	WT120C LED34S/840 PSD L1500	30 W
910500458246	WT120C LED40S/840 PSD L1200	36.5 W
910500458247	WT120C LED60S/840 PSD L1500	49.5 W
910500458248	WT120C LED22S/840 PSD L1200 EL3	22.5 W
910500458249	WT120C LED40S/840 PSD L1200 EL3	39.5 W
910500458250	WT120C LED34S/840 PSD L1500 EL3	33 W
910500458251	WT120C LED60S/840 PSD L1500 EL3	52 W
910500458794	WT120C LED22S/840 PSU TW3 L1200	23.5 W
910500458795	WT120C LED34S/840 PSU TW3 L1500	29.5 W

Order Code	Full Product Name	Initial input power
910500458796	WT120C LED40S/840 PSU TW3 L1200	35.5 W
910500458797	WT120C LED60S/840 PSU TW3 L1500	48 W
910500465266	WT120C LED40S/840 IA1 L1200	36.5 W
910500465267	WT120C LED60S/840 IA1 L1500	49.5 W
910500465326	WT120C LED40S/840 IA1 L1200 EL3	39.5 W
910500465327	WT120C LED60S/840 IA1 L1500 EL3	52 W
910500465651	WT120C LED80S/840 PSU L1500	68 W
910500465652	WT120C LED80S/840 PSD L1500	68 W
910500465653	WT120C LED80S/840 PSU TW3 L1500	68 W
910500465654	WT120C LED80S/840 PSU L1500 EL3	71 W
910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	32 W
910500459302	WT120C LED60S/840 PSU WEC L1500	48 W
910505100038	WT120C G2 LED19S/840 PSD L600	16 W
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	21 W
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	26 W
910505100044	WT120C G2 LED27S/840 PSD L1200	22 W
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	27 W
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	30 W
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	30 W
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	30 W
910505100052	WT120C G2 LED40S/840 IA1 L1200	30 W
910505100053	WT120C G2 LED40S/840 PSD L1200	30 W
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	35 W
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	34.5 W

CoreLine Waterproof

Order Code	Full Product Name	Initial input power
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	35 W
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	25.5 W
910505100061	WT120C G2 LED34S/840 PSD L1500	25.5 W
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	30.5 W
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	30.5 W
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	45 W
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	45 W
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	45 W
910505100071	WT120C G2 LED60S/840 IA1 L1500	45.5 W
910505100072	WT120C G2 LED60S/840 PSD L1500	45 W
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	50 W
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	50 W
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	51 W
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	61 W

Order Code	Full Product Name	Initial input power
910505100079	WT120C G2 LED80S/840 PSD L1500	61 W
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	66 W
911401823480	WT120C G2 LED19S/840 PSU L600	15 W
911401823580	WT120C G2 LED27S/840 PSU L1200	20.5 W
911401823680	WT120C G2 LED34S/840 PSU L1500	24.3 W
911401823780	WT120C G2 LED40S/840 PSU L1200	28.6 W
911401823880	WT120C G2 LED60S/840 PSU L1500	42.9 W
911401823980	WT120C G2 LED80S/840 PSU L1500	57.1 W
911401836980	WT120C G2 LED18S/840 PSU PCO L600	15 W
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	20.5 W
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	24.3 W
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	28.6 W
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	42.9 W
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	57.1 W

Mechanical and Housing

Order Code	Full Product Name	Diameter	Width
910500453335	WT120C LED18S/840 PSU L600	-	-
910500453336	WT120C LED22S/840 PSU L1200	-	-
910500453337	WT120C LED34S/840 PSU L1500	-	-
910500453338	WT120C LED40S/840 PSU L1200	-	-
910500453339	WT120C LED60S/840 PSU L1500	-	-
910500454298	WT120C LED22S/840 PSU L1200 EL1	-	-
910500454299	WT120C LED40S/840 PSU L1200 EL1	-	-
910500454301	WT120C LED34S/840 PSU L1500 EL1	-	-
910500454302	WT120C LED60S/840 PSU L1500 EL1	-	-
910500454303	WT120C LED22S/840 PSU L1200 EL3	-	-
910500454304	WT120C LED40S/840 PSU L1200 EL3	-	-
910500454305	WT120C LED34S/840 PSU L1500 EL3	-	-
910500454306	WT120C LED60S/840 PSU L1500 EL3	-	-
910500458243	WT120C LED18S/840 PSD L600	-	-
910500458244	WT120C LED22S/840 PSD L1200	-	-
910500458245	WT120C LED34S/840 PSD L1500	-	-
910500458246	WT120C LED40S/840 PSD L1200	-	-
910500458247	WT120C LED60S/840 PSD L1500	-	-
910500458248	WT120C LED22S/840 PSD L1200 EL3	-	-
910500458249	WT120C LED40S/840 PSD L1200 EL3	-	-
910500458250	WT120C LED34S/840 PSD L1500 EL3	-	-
910500458251	WT120C LED60S/840 PSD L1500 EL3	-	-
910500458794	WT120C LED22S/840 PSU TW3 L1200	-	- mm
910500458795	WT120C LED34S/840 PSU TW3 L1500	-	- mm
910500458796	WT120C LED40S/840 PSU TW3 L1200	-	- mm
910500458797	WT120C LED60S/840 PSU TW3 L1500	-	-
910500465266	WT120C LED40S/840 IA1 L1200	-	-
910500465267	WT120C LED60S/840 IA1 L1500	-	-
910500465326	WT120C LED40S/840 IA1 L1200 EL3	-	-
910500465327	WT120C LED60S/840 IA1 L1500 EL3	-	-
910500465651	WT120C LED80S/840 PSU L1500	-	-
910500465652	WT120C LED80S/840 PSD L1500	-	-
910500465653	WT120C LED80S/840 PSU TW3 L1500	-	-
910500465654	WT120C LED80S/840 PSU L1500 EL3	-	-

Order Code	Full Product Name	Diameter	Width
910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	-	-
910500459302	WT120C LED60S/840 PSU WEC L1500	-	-
910505100038	WT120C G2 LED19S/840 PSD L600	-	-
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	-
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	-	-
910505100044	WT120C G2 LED27S/840 PSD L1200	-	-
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	-	-
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	-
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-	-
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	-
910505100052	WT120C G2 LED40S/840 IA1 L1200	-	-
910505100053	WT120C G2 LED40S/840 PSD L1200	-	-
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	-	-
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	-
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	-	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	-
910505100061	WT120C G2 LED34S/840 PSD L1500	-	-
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	-	-
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	-	-
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	-
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	-
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	-
910505100071	WT120C G2 LED60S/840 IA1 L1500	-	-
910505100072	WT120C G2 LED60S/840 PSD L1500	-	-
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	-	-
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	-
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	-	-
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	-
910505100079	WT120C G2 LED80S/840 PSD L1500	-	-
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	-	-
911401823480	WT120C G2 LED19S/840 PSU L600	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-	-
911401823680	WT120C G2 LED34S/840 PSU L1500	-	-
911401823780	WT120C G2 LED40S/840 PSU L1200	-	-

CoreLine Waterproof

Order Code	Full Product Name	Diameter	Width
911401823880	WT120C G2 LED60S/840 PSU L1500	-	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-	-

Order Code	Full Product Name	Diameter	Width
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
910500453335	WT120C LED18S/840 PSU L600	-	-
910500453336	WT120C LED22S/840 PSU L1200	-	-
910500453337	WT120C LED34S/840 PSU L1500	-	-
910500453338	WT120C LED40S/840 PSU L1200	-	-
910500453339	WT120C LED60S/840 PSU L1500	-	-
910500454298	WT120C LED22S/840 PSU L1200 EL1	-	-
910500454299	WT120C LED40S/840 PSU L1200 EL1	-	-
910500454301	WT120C LED34S/840 PSU L1500 EL1	-	-
910500454302	WT120C LED60S/840 PSU L1500 EL1	-	-
910500454303	WT120C LED22S/840 PSU L1200 EL3	-	-
910500454304	WT120C LED40S/840 PSU L1200 EL3	-	-
910500454305	WT120C LED34S/840 PSU L1500 EL3	-	-
910500454306	WT120C LED60S/840 PSU L1500 EL3	-	-
910500458243	WT120C LED18S/840 PSD L600	-	-
910500458244	WT120C LED22S/840 PSD L1200	-	-
910500458245	WT120C LED34S/840 PSD L1500	-	-
910500458246	WT120C LED40S/840 PSD L1200	-	-
910500458247	WT120C LED60S/840 PSD L1500	-	-
910500458248	WT120C LED22S/840 PSD L1200 EL3	-	-
910500458249	WT120C LED40S/840 PSD L1200 EL3	-	-
910500458250	WT120C LED34S/840 PSD L1500 EL3	-	-
910500458251	WT120C LED60S/840 PSD L1500 EL3	-	-
910500458794	WT120C LED22S/840 PSU TW3 L1200	-	-
910500458795	WT120C LED34S/840 PSU TW3 L1500	-	-
910500458796	WT120C LED40S/840 PSU TW3 L1200	-	-
910500458797	WT120C LED60S/840 PSU TW3 L1500	-	-
910500465266	WT120C LED40S/840 IA1 L1200	-	-
910500465267	WT120C LED60S/840 IA1 L1500	-	-
910500465326	WT120C LED40S/840 IA1 L1200 EL3	-	-
910500465327	WT120C LED60S/840 IA1 L1500 EL3	-	-
910500465651	WT120C LED80S/840 PSU L1500	30000 h	15000 h
910500465652	WT120C LED80S/840 PSD L1500	30000 h	15000 h
910500465653	WT120C LED80S/840 PSU TW3 L1500	30000 h	15000 h
910500465654	WT120C LED80S/840 PSU L1500 EL3	30000 h	15000 h
910500459301	WT120C LED40S/840 PSU TW1 WEC L1200	-	-
910500459302	WT120C LED60S/840 PSU WEC L1500	-	-
910505100038	WT120C G2 LED19S/840 PSD L600	-	-
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	-
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	-	-

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
910505100044	WT120C G2 LED27S/840 PSD L1200	-	-
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	-	-
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	-
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-	-
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	-
910505100052	WT120C G2 LED40S/840 IA1 L1200	-	-
910505100053	WT120C G2 LED40S/840 PSD L1200	-	-
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	-	-
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	-
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	-	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	-
910505100061	WT120C G2 LED34S/840 PSD L1500	-	-
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	-	-
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	-	-
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	-
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	-
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	-
910505100071	WT120C G2 LED60S/840 IA1 L1500	-	-
910505100072	WT120C G2 LED60S/840 PSD L1500	-	-
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	-	-
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	-
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	-	-
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	-
910505100079	WT120C G2 LED80S/840 PSD L1500	-	-
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	-	-

CoreLine Waterproof

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401823480	WT120C G2 LED19S/840 PSU L600	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-	-
911401823680	WT120C G2 LED34S/840 PSU L1500	-	-
911401823780	WT120C G2 LED40S/840 PSU L1200	-	-
911401823880	WT120C G2 LED60S/840 PSU L1500	-	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-	-

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-	-

