



# Product Description

## CDM

Compact reflector discharge lamps with quartz outer bulb

### Benefits

- High beam intensities thanks to the short arc, axially mounted discharge arc and compact lamp dimensions
- Sparkling light for fresh white colour impression
- Stable colour over lifetime
- Excellent colour rendering
- Low operating costs through high lamp efficacy
- Long life compared with halogen lamps
- Low heat output increases personal comfort
- UV block reduces risk of fading

### Features

- Long life
- High efficiency
- High colour rendering index (Ra 90)

### Application

- Advertising/text projection
- Fibre optics
- Decorative outdoor, architectural lighting
- Shops and shop windows

### Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

CDM

Versions



Dimensional drawing



Product	D (max)	X	C (max)
CDM-SA/R 150W/942 UNP/1	95.3 mm	280 mm	106 mm

