



Product Description

CDM

Compact reflector discharge lamps with quartz outer bulb

Benefits

- High beam intensities thanks to the short arc, axially mounted discharge arc and compact lamp dimensions
- Sparkling light for fresh white colour impression
- Stable colour over lifetime
- Excellent colour rendering
- Low operating costs through high lamp efficacy
- Long life compared with halogen lamps
- Low heat output increases personal comfort
- UV block reduces risk of fading

Features

- Long life
- High efficiency
- High colour rendering index (Ra 90)

Application


- Advertising/text projection
- Fibre optics
- Decorative outdoor, architectural lighting
- Shops and shop windows

CDM

Versions



Dimensional drawing



| Product | D (max) | X | C (max) |
|-------------------------|---------|--------|---------|
| CDM-SA/R 150W/942 UNP/1 | 95.3 mm | 280 mm | 106 mm |

