



CDM short arc reflector lamps – perfect colors, long life

CDM

The perfect color rendering and long life of these Ceramic Discharge Metal-halide lamps make them ideal for fiber optics lighting systems in shop displays, decorative lighting and swimming pool illumination. They can be mounted in color changing projectors.

Benefits

- Low cost of ownership
- Perfect colors

Features

- Long life
- High efficiency
- High color rendering index (Ra 90)

Application

- Shops
- Side lighting
- Architainment (e.g. swimming pools)


CDM

Versions



CDM-SA/R 150W

Dimensional drawing



| Product | D (max) | X | C (max) |
|-------------------------|---------|--------|---------|
| CDM-SA/R 150W/942 UNP/1 | 95.3 mm | 280 mm | 106 mm |

