



Product Description

CDM-SA/T

CDM-SA/T – the greener way to light up the night With a high luminous efficacy producing more lumens per watt than standard Architainment lamps, the CDM-SA/T is the greener alternative to light up the night. In addition, the optimal lamp filling and short arc of the lamp create a high beam intensity and excellent colour rendering.

Benefits

- High beam intensities thanks to the short arc, axially mounted discharge arc and compact lamp dimensions
- Sparkling light for fresh white colour impression
- Stable colour over lifetime
- Excellent colour rendering
- Low operating costs through high lamp efficacy
- Long life compared with halogen lamps
- Low heat output increases personal comfort
- UV block reduces risk of fading

Features

- High luminous efficacy
- Compact arc
- Optimal lamp filling

Application

- Advertising/text projection
- Fibre optics
- Decorative outdoor, architectural lighting
- Shops and shop windows

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

CDM-SA/T

Versions



Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
CDM-SA/T	20 mm	6	55 mm	57 mm	56	110 mm	31 mm	30	29 mm
150W/942		mm			mm			mm	
1CT/12									

