



Architectural MSA – double ended night colors

Architectural MSA

The high luminous efficacy and optimal lamp filling of the double ended Architectural MSA lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Vorteile

- Optimale Farbwiedergabe

Merkmale

- Lange Lebensdauer
- Kompakter Lichtbogen
- Ausgezeichnete Farbeigenschaften

Anwendung

- Dynamische Architekturbeleuchtung

Hinweise

- Es ist sehr unwahrscheinlich, dass der Glasbruch einer Lampe negative Auswirkungen auf Ihre Gesundheit hat. Wenn es zu einem Glasbruch kommt, lüften Sie den Raum 30 Minuten lang und entfernen Sie die Splitter möglichst mit Handschuhen. Legen Sie die Splitter in eine verschließbaren Plastikbeutel und geben Sie ihn beim Werkstoffhof zum Recycling ab. Benutzen Sie keinen Staubsauger.


Architectural MSA

Versions



XPPR XDMSA 0003

Abmessungsskizzen



Product	D (max)	O	C (max)
MSA 2500 DE UNP/1	41 mm	25 mm	364 mm

