



Architectural MSA – double ended night colors

Architectural MSA

The high luminous efficacy and optimal lamp filling of the double ended Architectural MSA lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Benefits

- Optimal colour rendering
- Extended service life

Features

- Compact arc
- Optimum light collection efficiency
- Universal burning position

Application


- Dynamic architectural lighting

Architectural MSA

Versions



Dimensional drawing



Product	D (max)	O	C (max)
MSA 2500 DE UNP/1	41 mm	25 mm	364 mm

