



MSD Platinum – The power to light your creativity

MSD Platinum

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Vorteile

- Lange und zuverlässige Lebensdauer (2000 h)
- Hohe Lichtbündelintensität
- Möglichkeit zur Schaffung kleinerer und leichter Leuchten
- Perfekte Ausrichtung und Lampenwechsel in Sekundenschnelle. Erneueres optisches System mit maximaler Lichtabstrahlung
- Hohe wahrgenommene Helligkeit

Merkmale

- Philips MSD-Technologie
- Sehr kurzer Lichtbogen
- Kleines, kompaktes Design
- Reflektorlampe
- Hohe ähnlichste Farbtemperatur

Anwendung


- Events
- Shows/Theater
- Tournée/Bühne

MSD Platinum

Versions



Abmessungsskizzen



Product	D (max)	T (max)	O	C (max)
MSD Platinum 2 R 1CT/8	46,5 mm	13,5 mm	1,2 mm	57,1 mm

