



MSR Gold™ SA Double Ended – for extended performance

MSR Gold™ SA Double Ended

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Benefits

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Pure, white light; colour point close to black body line. Consistent colour impression over MSR Range
- Reduces early lamp or lamp holder failures

Features

- Philips Pinch Protection
- MSR filling
- Gold plated lamp caps

Application

- Entertainment

MSR Gold™ SA Double Ended

Versions



Dimensional drawing

Product	D (max)	O	A	C (max)		
MSR Gold™ 1510 SA/DE 1CT/4	23.2 mm	7.0 mm	114.8 mm	136 mm		
MSR Gold™ 700 SA/2 DE 1CT/4	19 mm	4.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold™ 575 SA/2 DE 1CT/40	18.5 mm	5.0 mm	69.6 mm	70.4 mm	70 mm	92 mm
MSR Gold™ 1200 SA/DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold™ 1200 SA/2 DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold™ 1510 SA/1 DE 1CT/4	115.2 mm	114.4 mm	114.8 mm	136 mm	23 mm	7 mm

General Information

Life To 50% Failures (Nom)	750 h
Operating Position	UNIVERSAL

Controls and Dimming

Order Code	Full Product Name	Dimmable
928099605115	MSR Gold™ 1200 SA/DE 1CT/4	no
928174705115	MSR Gold™ 700 SA/2 DE 1CT/4	no
928175305115	MSR Gold™ 1200 SA/2 DE 1CT/4	no

Order Code	Full Product Name	Dimmable
928176605115	MSR Gold™ 1510 SA/DE 1CT/4	yes
928175105114	MSR Gold™ 575 SA/2 DE 1CT/40	no
928410005115	MSR Gold™ 1510 SA/1 DE 1CT/4	Yes

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
928099605115	MSR Gold™ 1200 SA/DE 1CT/4	13.6 A	1200 W
928174705115	MSR Gold™ 700 SA/2 DE 1CT/4	11.5 A	700 W
928175305115	MSR Gold™ 1200 SA/2 DE 1CT/4	13.6 A	1200 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
928176605115	MSR Gold™ 1510 SA/DE 1CT/4	13.5 A	1510 W
928175105114	MSR Gold™ 575 SA/2 DE 1CT/40	7 A	575 W
928410005115	MSR Gold™ 1510 SA/1 DE 1CT/4	13.4 A	1510 W

General Information

MSR Gold™ SA Double Ended

Order Code	Full Product Name	Cap-Base	Main	System
			Application	Description
928099605115	MSR Gold™ 1200 SA/DE 1CT/4	SFC10-4	Entertainment	SA/DE
928174705115	MSR Gold™ 700 SA/2 DE 1CT/4	SFC10-4	Studio/Disco	SA/2 DE
928175305115	MSR Gold™ 1200 SA/2 DE 1CT/4	SFC10-4	Entertainment	SA/2 DE

Order Code	Full Product Name	Cap-Base	Main	System
			Application	Description
928176605115	MSR Gold™ 1510 SA/DE 1CT/4	SFC10-4	Entertainment	SA/DE
928175105114	MSR Gold™ 575 SA/2 DE 1CT/40	SFC-11	Entertainment	SA/2 DE
928410005115	MSR Gold™ 1510 SA/1 DE 1CT/4	SFC10-4	Entertainment	SA/DE

Light Technical

Order Code	Full Product Name	Colour Code	Correlated Colour	Colour Rendering	Colour Rendering	Luminous Flux (Min)	Luminous Flux (Nom)
			Temperature (Nom)	Index (Min)	Index (Nom)		
928099605115	MSR Gold™ 1200 SA/DE 1CT/4	-	6000 K	-	85	92700 lm	103000 lm
928174705115	MSR Gold™ 700 SA/2 DE 1CT/4	-	7500 K	62	75	43200 lm	48000 lm
928175305115	MSR Gold™ 1200 SA/2 DE 1CT/4	-	7500 K	-	85	90000 lm	100000 lm
928176605115	MSR Gold™ 1510 SA/DE 1CT/4	-	6000 K	-	85	-	140000 lm
928175105114	MSR Gold™ 575 SA/2 DE 1CT/40	2	7500 K	-	75	39000 lm	42000 lm
928410005115	MSR Gold™ 1510 SA/1 DE 1CT/4	-	5600 K	-	90	-	141000 lm

Colour Rendering Diagrams

